



Eaton 812027FULL-0164X

Eaton, Alarms & signalling devices, Fulleon, Solista LX Ceiling LED beacon, Red flash, Red housing, Shallow red base (SOL-LX-C/RF/R1/S)

□□□□

PRODUCT NAME	Eaton Solista LX Visual alarm beacon
CATALOG NUMBER	812027FULL-0164X
PRODUCT LENGTH/DEPTH	37 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	93 mm
PRODUCT WEIGHT	0.1 kg
COMPLIANCES	EN

NOMINAL VOLTAGE	24 V
VOLTAGE TYPE	DC
ELECTRICITY CONSUMPTION	0.025 A
POWER	1.5 W
LENS COLOR	Colourless
MATERIAL HOUSING	Plastic
COLOR HOUSING	Other
MOUNTING METHOD	Surface mounting
NUMBER OF MODES	4
STANDBY-TIME UP TO	0 hour
AMBIENT TEMPERATURE - MAX	70 °C
AMBIENT TEMPERATURE - MIN	-25 °C
LAMP TYPE	LED not exchangeable
LAMP HOLDER	Other
DEGREE OF PROTECTION (IP)	IP33
ADDRESSING MODE	Hard addressing
ALARM CURRENT - MAX	51 mA
ALARM CURRENT - MIN	9 mA
CONSTRUCTION MATERIAL	ABS/FR
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
OPERATING TEMPERATURE - MAX	70 °C
OPERATING TEMPERATURE - MIN	-25 °C
STANDBY CURRENT	0
SYSTEM TYPOLOGY	Conventional (Non-addressable)
PRODUCT BRANDING	Eaton
NOMINAL VOLTAGE - MIN	12 V
NOMINAL VOLTAGE - MAX	48 V
ELECTRICITY CONSUMPTION - MIN	0.018 A
ELECTRICITY CONSUMPTION - MAX	0.051 A
INTEGRATED FUNCTION	Flashlight

EN CERTIFICATION STANDARDS	EN54 Pt23 (Visual Alarms)
CABLE ENTRY	Rear
MOUNTING POSITION	Ceiling in open areas
LIGHT COLOR	Red
SYSTEM WIRING	0.5 - 2.5 mm
DIMMABLE	No
FUNCTION ROTATING LIGHT	NO
WITH INFRARED	NO

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

