



□□□□□

Eaton 9106-9295

Eaton 93PR UPS, ENG

□□□□

PRODUCT NAME	Eaton 93PR UPS
CATALOG NUMBER	9106-9295
PRODUCT LENGTH/DEPTH	1100 mm
PRODUCT HEIGHT	2020 mm
PRODUCT WIDTH	600 mm
PRODUCT WEIGHT	0.001 kg
CERTIFICATIONS	CE

AUDIBLE ALARMS	Yes
AUTO SHUTDOWN FUNCTION	Yes
INTERNAL BATTERY INCLUDED	Yes
USER REPLACABLE BATTERIES	Yes
BATTERY CHARGER TYPE	ABM technology
EXTERNAL BATTERY CONNECTION	Hardwired
BTU RATING	4100*N
COLOR	Black
COMMUNICATION	Relay-MS, Network-MS, Modbus Card-MS,PXGMS
CONSTRUCTION TYPE	Free standing model
IMPROVED EFFICIENCY MODE	High Efficiency
NUMBER OF COMMUNICATION SLOTS	3
FEED TYPE	AC
FORM FACTOR	Modular
HOT-SWAPPABLE POWER MODULES	Yes
INPUT CONNECTION	Fixed connection
INPUT CURRENT DISTORTION	3 %
INPUT NOMINAL VOLTAGE	380Y/220V nominal (400V/230V, 415Y/240V)
POWER MODULE RATING - MAX	25 kVA
NOISE LEVEL (STANDARD MODE)	<70 dBA at 1 meter
OPERATING TEMPERATURE	0°C - 40°C,Batteries recommended max. +25°C
OUTPUT FREQUENCY	50 Hz (50/60 Hz programmable)
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE REGULATION	±3%
OVERALL EFFICIENCY	96 %
OVERLOAD	10 min 105-110% load□60 sec 111-125% load□10 sec 126-150% load□300 ms >150% load
NUMBER OF PARALLEL UNITS	4

PHASE (INPUT)	3
PHASE (OUTPUT)	3
POTENTIAL FREE SWITCH CONTACT	No
RACK MOUNTING KIT INCLUDED	No
SNMP	Yes
SOFTWARE COMPATIBILITY	IPP, IPM
STANDARD FACTORY WARRANTY	1 years
START-ON-BATTERY	Yes
STORAGE TEMPERATURE	-15°C-55°C without batteries
TOPOLOGY	Online/Double-conversion
TYPE OF INTERFACE	RS-232, USB
INTERNAL MAINTENANCE BYPASS	Yes
USER INTERFACE (HMI)	7" HMI
KVA RATING	75 W
VOLTAGE	380Y/220V
WATTAGE	75000 W
APPLICATION	Data center/ facility/IT
EFFICIENCY (IMPROVED EFFICIENCY MODE)	99 %
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	1 %
INTEGRATED FUNCTIONALITY	Network Mangement Modular
INPUT FREQUENCY - MIN	40 Hz
INPUT FREQUENCY - MAX	72 Hz
INPUT VOLTAGE - MIN	187 V
INPUT VOLTAGE - MAX	276 V
DEGREE OF PROTECTION	IP20

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

