



□□□□□

## Eaton CPS152 202 SA

Eaton Crouse-Hinds series Arktite CPS receptacle assembly, 20A, Dead end, Two-wire, three-pole, Brass contact, 60 Hz, Style 2, 1 HP, Copper-free aluminum, Two-gang, Factory sealed, 3/4", Delayed action circuit breaking, 125-250 Vac/18 Vdc

□□□□

|                             |                                                           |
|-----------------------------|-----------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Arktite CPS receptacle assembly |
| <b>CATALOG NUMBER</b>       | CPS152 202 SA                                             |
| <b>UPC</b>                  | 782274467436                                              |
| <b>PRODUCT LENGTH/DEPTH</b> | 7.19 in                                                   |
| <b>PRODUCT HEIGHT</b>       | 6.72 in                                                   |
| <b>PRODUCT WIDTH</b>        | 8 in                                                      |
| <b>PRODUCT WEIGHT</b>       | 4.15 lb                                                   |

| □□□□                 |                                            |
|----------------------|--------------------------------------------|
| AREA CLASSIFICATION  | Hazardous/Classified Locations             |
| STANDARDS TYPE       | NEC/CEC                                    |
| NEC HAZARDOUS RATING | Class I, Division 2<br>Class I, Division 1 |
| SPECIAL FEATURES     | Factory sealed                             |
| TYPE                 | Delayed action circuit breaking            |
| AMPERAGE RATING      | 20A                                        |
| VOLTAGE RATING       | 125-250 Vac/18 Vdc                         |
| CONTACT MATERIAL     | Brass                                      |
| BACK BOX STYLE       | Dead end                                   |
| CONFIGURATION        | Two-wire, three-pole                       |
| FREQUENCY RATING     | 60 Hz                                      |
| GROUNDING STYLE      | Style 2                                    |
| HORSEPOWER           | 1 hp                                       |
| MATERIAL             | Copper-free aluminum                       |
| NUMBER OF GANGS      | Two-gang                                   |
| TRADE SIZE           | 3/4"                                       |

| □□       |                                                                                                               |
|----------|---------------------------------------------------------------------------------------------------------------|
| □□□□□    | <a href="#">IF 165 - CPS Receptacles</a>                                                                      |
|          | <a href="#">IF 1424 - DSD, GFS, CPS and ENR Replacement Covers</a>                                            |
|          | <a href="#">IF 654 - CPS 20A Receptacles</a>                                                                  |
| □□□□□□□□ | <a href="#">Eaton Specification Sheet - CPS152 202 SA</a>                                                     |
| □□□□     | <a href="#">Arktite CPS and CPP Explosionproof Receptacles and Plugs catalog page</a>                         |
| □□□□     | <a href="#">Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification</a> |
|          | <a href="#">Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification</a>       |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| □□:             |



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the latest product and support information.

