



## Eaton CSCXS16USB

16-Device USB Charging Station Cabinet with Sync for iPad and Android Tablets, Wall-Mount and Cart Options, 230V, Schuko CEE7 to C13 Plug, Black



<b>PRODUCT NAME</b>	Eaton Tripp Lite series mobile charging cart
<b>CATALOG NUMBER</b>	CSCXS16USB
<b>UPC</b>	037332285034
<b>PRODUCT LENGTH/DEPTH</b>	20.2 in
<b>PRODUCT HEIGHT</b>	18.8 in
<b>PRODUCT WIDTH</b>	30.33 in
<b>PRODUCT WEIGHT</b>	85.98 lb
<b>COMPLIANCES</b>	CE Marked REACH RoHS
<b>CERTIFICATIONS</b>	CAN/CSA C22.2 UL 62368-1



Powering Business Worldwide



<b>FREQUENCY RATING</b>	50 Hz
<b>CHARGING PORTS DETAILS</b>	Pass through
<b>NUMBER OF CHARGING PORTS</b>	16
<b>TOTAL CHARGING AMPS</b>	40
<b>TOTAL CHARGING WATTS</b>	200
<b>PRODUCT TYPE</b>	Multi-Device Charger
<b>DEVICE COMPATIBILITY</b>	Tablet
<b>FREQUENCY COMPATABILITY</b>	50 Hz
<b>COLOR</b>	Black
<b>INPUT PLUG TYPE</b>	Schuko
<b>MATERIAL</b>	Steel
<b>CHARGING PORTS / AMPS</b>	2.4A
<b>INPUT CORD LENGTH</b>	12 ft
<b>INPUT FREQUENCY</b>	50 Hz
<b>CHARGING METHOD</b>	USB
<b>INPUT NOMINAL VOLTAGE</b>	230 VAC
<b>PRODUCT FEATURES</b>	EMI/RFI Line Noise Protection Locking Cord Management Built-In Circuit Breaker Overcurrent Protection Flow-Through Ventilation Overcharge Protection
<b>RELATIVE HUMIDITY</b>	5% TO 95% RH (NON CONDENSING)
<b>OPERATING HUMIDITY RANGE</b>	5% TO 95% RH (NON CONDENSING)
<b>OPERATING TEMPERATURE RANGE</b>	32° to 86°F (0° to 30°C)
<b>STORAGE TEMPERATURE RANGE</b>	5° to 122°F (-15° to 50°C)
<b>PRODUCT HIGHLIGHTS</b>	Ships fully assembled for immediate placement in an office, classroom, etc. Secures up to 16 mobile devices behind locking doors to help prevent tampering 230V cabinet features 3.7 m cord with Schuko-to-C13 plug for reaching distant outlets Removable dividers

	accommodate thicker devices such as battery chargers Supports wall mounting or desktop/floor placement in a structurally sound area
<b>CHARGING FORM FACTOR</b>	Stationary cabinet
<b>CHARGING PORT TYPE</b>	USB A (FEMALE)
<b>DEVICE SLOTS</b>	16
<b>NUMBER OF SHELVES</b>	1
<b>POWER CONSUMPTION</b>	56 W
<b>VOLTAGE COMPATIBILITY (VAC)</b>	230 VAC
<b>CHARGING STATION FORM FACTOR</b>	Stationary cabinet
<b>CHARGING AMPS PER PORT</b>	2.4 A 2.4A
<b>LOCK</b>	Key

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House  
30 Pembroke Road  
Dublin 4, □□□□  
Eaton.com

