

Eaton ED2N42171112

Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture, 3/4", Myers conduit hubs, stainless steel, one entry at each end, 4 ft, Polycarbonate lens, T8 bi-pin, Fiberglass-reinforced polyester, 2-lamp, Ceiling, 120-277 Vac, 32W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture
CATALOG NUMBER	ED2N42171112
UPC	662276645165
PRODUCT LENGTH/DEPTH	53 in
PRODUCT HEIGHT	5.6 in
PRODUCT WIDTH	8.5 in
PRODUCT WEIGHT	17 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
LAMP LENGTH	4 ft
LIGHT TYPE	T8 bi-pin
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MOUNTING	Ceiling
ENTRY SIZE	3/4"
ENTRY TYPE	Myers hubs, stainless steel, one entry at each end
WATTAGE	32W
NUMBER OF LAMPS	2-lamp
MATERIAL	Fiberglass-reinforced polyester
LENS MATERIAL	Polycarbonate

3D

[Eaton Crouse-Hinds ED2N42171112 3D drawing](#)

[IF LBL1584 - Pauluhn ECOS ED2N Series Linear Fluorescent](#)

[Eaton Specification Sheet - ED2N42171112](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent brochure](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent catalog page](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures UL certification](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures Canadian certification](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

