

## Eaton ENR22151

Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly, 15A, Double, 50-400 Hz, Copper-free aluminum, 5-15R, Two-gang, Dead end, 3/4", 125 Vac

|                             |                                                                  |
|-----------------------------|------------------------------------------------------------------|
|                             |                                                                  |
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly |
| <b>CATALOG NUMBER</b>       | ENR22151                                                         |
| <b>UPC</b>                  | 662276542198                                                     |
| <b>PRODUCT LENGTH/DEPTH</b> | 7.56 in                                                          |
| <b>PRODUCT HEIGHT</b>       | 6.72 in                                                          |
| <b>PRODUCT WIDTH</b>        | 8 in                                                             |
| <b>PRODUCT WEIGHT</b>       | 0.01 lb                                                          |

|                             |                                                                                                         |
|-----------------------------|---------------------------------------------------------------------------------------------------------|
| <b>AREA CLASSIFICATION</b>  | Hazardous/Classified Locations                                                                          |
| <b>STANDARDS TYPE</b>       | NEC/CEC                                                                                                 |
| <b>NEC HAZARDOUS RATING</b> | Class II, Division 1<br>Class II, Division 2<br>Class I, Division 1<br>Class I, Division 2<br>Class III |
| <b>NEMA RATING</b>          | 3<br>12<br>9<br>7                                                                                       |
| <b>AMPERAGE RATING</b>      | 15A                                                                                                     |
| <b>VOLTAGE RATING</b>       | 125 Vac                                                                                                 |
| <b>COVER TYPE</b>           | Double                                                                                                  |
| <b>MATERIAL</b>             | Copper-free aluminum                                                                                    |
| <b>NUMBER OF GANGS</b>      | Two-gang                                                                                                |
| <b>STYLE</b>                | Dead end                                                                                                |
| <b>TRADE SIZE</b>           | 3/4"                                                                                                    |
| <b>FREQUENCY RATING</b>     | 50-400 Hz                                                                                               |
| <b>NEMA CONFIGURATION</b>   | 5-15R                                                                                                   |

|                               |                                                                                                                                                                                                                                  |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>3D CAD DRAWING PACKAGE</b> | <a href="#">Eaton Crouse-Hinds ENR22151 3D drawing</a>                                                                                                                                                                           |
|                               | <a href="#">IF 1424 - DSD, GFS, CPS and ENR Replacement Covers</a><br><br><a href="#">IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs</a>                                                                                  |
|                               | <a href="#">Ark-Gard ENR Value Explosionproof NEMA Locking Devices catalog page</a>                                                                                                                                              |
|                               | <a href="#">Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP</a><br><br><a href="#">Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP</a> |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: