



□□□□□

Eaton IHB16LP1/UNV1 S891

Eaton Crouse-Hinds series IHB industrial high bay LED fixture, Cool white, Non-dim driver, 250W-500W HID or 4-lamp T5HO, Diffused glass lens, 16000 lm, 116 lm/W, Aluminum, Pend mt, Wide, 3/4" trade size, 100-277 Vac, 127-250 Vdc, 145W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series IHB industrial high bay LED light fixture
CATALOG NUMBER	IHB16LP1/UNV1 S891
UPC	662276586710
PRODUCT LENGTH/DEPTH	18.83 in
PRODUCT HEIGHT	4.23 in
PRODUCT WIDTH	13.36 in
PRODUCT WEIGHT	18 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
----------------------------	----------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

Product specifications

LUMENS	16000
---------------	-------

LUMENS PER WATT	26W
------------------------	-----

COLOR TEMPERATURE	Cool white
--------------------------	------------

MOUNTING METHOD	Pendant
------------------------	---------

TRADE SIZE	100-240 Vac, 127-250 Vdc
-------------------	--------------------------

OPTICAL DISTRIBUTION	Wide
-----------------------------	------

DIMMING	Non-dimmable driver
----------------	---------------------

VOLTAGE RATING	100-277 Vac, 127-250 Vdc
-----------------------	--------------------------

FREQUENCY RATING	50/60 Hz
-------------------------	----------

MATERIAL	Aluminum
-----------------	----------

LENS MATERIAL	Diffused Glass
----------------------	----------------

WATTAGE	145W
----------------	------

EQUIVALENT LUMINAIRE	250W-500W HID or 4-lamp T5HO
-----------------------------	------------------------------

POWER FACTOR	0.99
---------------------	------

00000	IF 1726 - Industrial High Bay LED Light Fixture
00000000	Eaton Specification Sheet - IHB16LP1/UNV1 S891
0000	Crouse-Hinds series DLC approved lighting products
	Crouse-Hinds series Industrial High Bay LED brochure
	Crouse-Hinds series Global LED lighting portfolio
0000	Crouse-Hinds series industrial LED lighting solutions
	Crouse-Hinds series Industrial High Bay LED catalog page
	Industrial High Bay LED Light Fixtures UL certification (Luminaire Fittings)
0000	Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures Canadian certification
	Champ Pro PFM LED, Pauluhn Apex Industrial LED, Industrial High Bay LED and Weatherproof LED Light Fixtures UL certification
	Industrial High Bay LED Light Fixtures Canadian certification (Luminaire Fittings)

