



## Eaton KEY-KP01

Bus mounted keypad with prox reader

□□□□

<b>PRODUCT NAME</b>	Eaton surface mounted keypad for intruder system
<b>CATALOG NUMBER</b>	KEY-KP01
<b>PRODUCT LENGTH/DEPTH</b>	28 mm
<b>PRODUCT HEIGHT</b>	128 mm
<b>PRODUCT WIDTH</b>	128 mm
<b>PRODUCT WEIGHT</b>	0.22 kg
<b>CERTIFICATIONS</b>	CE marking



Powering Business Worldwide

□□□□

<b>TYPE</b>	Keypad
<b>BATTERY CHARGE OUTPUTS</b>	0
<b>COLOUR</b>	White
<b>COLOUR (ETIM)</b>	White
<b>CURRENT - MAX</b>	65 mA
<b>CURRENT NORMAL</b>	35 mA
<b>DATA SHEETS</b>	KEY-K series
<b>DEDICATED PA KEYS</b>	Yes
<b>DEVICE CONNECTIONS</b>	Wired
<b>DISPLAY</b>	Yes
<b>EN 50131 GRADE</b>	3
<b>ENVIRONMENTAL CLASS</b>	2
<b>EXPANSION PANEL</b>	No
<b>EXTERNAL PROX</b>	Yes
<b>INTERNAL PROX</b>	Yes
<b>LOUDSPEAKER CONNECTION</b>	No
<b>MOUNTING METHOD (ETIM)</b>	Surface mounting
<b>NUMBER OF GROUPS</b>	0
<b>OPERATING TEMPERATURE - MAX</b>	55 °C
<b>OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>RADIO FREQUENCY</b>	Not applicable
<b>RECHARGEABLE BATTERY</b>	Not applicable
<b>SUPPLY - MAX</b>	13.8 V
<b>SUPPLY - MIN</b>	10 V
<b>TOUCH PANEL</b>	No
<b>TRANSISTOR OUTPUTS</b>	1
<b>TYPE OF BUS DEVICE</b>	Keypad
<b>VDS CLASS</b>	None
<b>WITH LCD INDICATION</b>	Yes
<b>ZONE INPUTS</b>	0
<b>WITH RADIO RECEIVER</b>	NO
<b>WITH LED INDICATION</b>	YES
<b>SUITABLE FOR INTRUSION ALARM</b>	YES
<b>SUITABLE FOR FIRE ALARM</b>	NO
<b>WITH BUILT-IN CARD READER</b>	YES

□□

