



## Eaton MBP6K208

Eaton 9PX maintenance bypass, Hardwired input; Outputs: (2) L6-30R, Hardwired; rear rackmount, tower mount, or wall mount



<b>PRODUCT NAME</b>	Eaton 9PX maintenance bypass
<b>CATALOG NUMBER</b>	MBP6K208
<b>UPC</b>	743172043603
<b>PRODUCT LENGTH/DEPTH</b>	4.3 in
<b>PRODUCT HEIGHT</b>	5.1 in
<b>PRODUCT WIDTH</b>	7 in
<b>PRODUCT WEIGHT</b>	5.5 lb
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	EN 62040-3 EN 61000-4-3 IEC 61000-4-6 IEC 61000-4-5 EN 61000-4-2 IEC/EN 62040-1 IEC/EN 62040-2 EN 61000-4-4 Electrical fast transient IEC 61000-4-8 cULus Listed NOM



Powering Business Worldwide

<b>SPECIAL FEATURES</b>	Rear rack mount, tower mount or wall mount
<b>TOPOLOGY</b>	Online/Double-conversion
<b>COLOR</b>	Black/silver
<b>RACK MOUNTING KIT</b>	Yes

<b>PACKAGE CONTENTS</b>	<ul style="list-style-type: none"> <li>• MBP6K208 Maintenance Bypass</li> <li>• Input/output UPS cable set</li> <li>• (2) Cable glands</li> <li>• Mounting hardware</li> <li>• Installation and user manual</li> </ul>
-------------------------	--

<b>TYPE OF ACCESSORY</b>	Bypass
--------------------------	--------

<b>USED WITH</b>	9PX6K, 9PX5K, 9PX6KG, 9PX3K3UN, 9PX6K-L
------------------	---

<b>INPUT CONNECTION</b>	Hardwired
-------------------------	-----------

<b>RECEPTACLE</b>	(2) L6-30R, Hardwired
-------------------	-----------------------

<b>STANDARD FACTORY WARRANTY</b>	<ul style="list-style-type: none"> <li>• 3-YEAR FACTORY WARRANTY</li> <li>• - 3 years</li> <li>• - Parts, electronics and batteries coverage</li> <li>• - Standard ground shipping</li> <li>• - Technical support</li> </ul>
----------------------------------	--

<b>RELATIVE HUMIDITY</b>	0-95% non-condensing
--------------------------	----------------------

<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
--------------------------	---------------------------

<b>ACCESSORY CLASS</b>	UPS Accessories
------------------------	-----------------

<b>ACCESSORY TYPE</b>	Bypass Panel (Rack-Mount)
-----------------------	---------------------------

