



## Eaton P018-003

Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 3 ft. (0.91 m), Black

□□□□

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Tripp Lite series extension cord |
| <b>CATALOG NUMBER</b>       | P018-003                               |
| <b>UPC</b>                  | 037332168436                           |
| <b>PRODUCT LENGTH/DEPTH</b> | 5.6 in                                 |
| <b>PRODUCT HEIGHT</b>       | 0.2 in                                 |
| <b>PRODUCT WIDTH</b>        | 4.8 in                                 |
| <b>PRODUCT WEIGHT</b>       | 0.4 lb                                 |
| <b>COMPLIANCES</b>          | RoHS                                   |
| <b>CERTIFICATIONS</b>       | cUL Listed<br>UL Listed                |

| Specifications              |                                                                                                                                                                                                                                                                                                                                                                          |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| INPUT CURRENT -MAX          | 15 Ampere                                                                                                                                                                                                                                                                                                                                                                |
| OPERATING TEMPERATURE RANGE | -4° to 140°F (-20° to 60°C)                                                                                                                                                                                                                                                                                                                                              |
| STORAGE TEMPERATURE         | -4° to 140°F (-20° to 60°C)                                                                                                                                                                                                                                                                                                                                              |
| DEVICE COMPATIBILITY        | Network Switch<br>PDU<br>UPS                                                                                                                                                                                                                                                                                                                                             |
| AWG-SIZE                    | 14                                                                                                                                                                                                                                                                                                                                                                       |
| CABLE LENGTH                | 3 Foot                                                                                                                                                                                                                                                                                                                                                                   |
| NUMBER OF CONDUCTORS        | 3                                                                                                                                                                                                                                                                                                                                                                        |
| OPERATING HUMIDITY          | 10% to 65% RH                                                                                                                                                                                                                                                                                                                                                            |
| OUTER CABLE DIAMETER        | 9.3mm                                                                                                                                                                                                                                                                                                                                                                    |
| POWER CORD JACKET TYPE      | SJT                                                                                                                                                                                                                                                                                                                                                                      |
| STORAGE HUMIDITY RANGE      | 10% to 65% RH                                                                                                                                                                                                                                                                                                                                                            |
| WIRE SIZE (AWG) - MAX       | 2.08                                                                                                                                                                                                                                                                                                                                                                     |
| CABLE LENGTH RANGE          | Up to 4ft (up to 1M)                                                                                                                                                                                                                                                                                                                                                     |
| CABLE JACKET RATING         | VW-1                                                                                                                                                                                                                                                                                                                                                                     |
| CABLE JACKET COLOR          | Black                                                                                                                                                                                                                                                                                                                                                                    |
| PACKAGE CONTENTS            | P018-003 C14 to C15<br>Power Cable, 3 ft. (0.9 m),<br>Black                                                                                                                                                                                                                                                                                                              |
| CONNECTOR COLOR             | Black                                                                                                                                                                                                                                                                                                                                                                    |
| CONNECTOR TYPE              | Power                                                                                                                                                                                                                                                                                                                                                                    |
| PRODUCT FEATURES            | High Voltage                                                                                                                                                                                                                                                                                                                                                             |
| CABLE JACKET MATERIAL       | PVC                                                                                                                                                                                                                                                                                                                                                                      |
| CONNECTOR STYLE             | Straight                                                                                                                                                                                                                                                                                                                                                                 |
| PRODUCT HIGHLIGHTS          | C14 to C15 power cable replaces or upgrades original manufacturer's power cord<br>Recommended for powering PoE switches with high-wattage power supplies<br>3 ft. length allows flexibility in placing devices, while avoiding cable clutter<br>Lifetime limited warranty (Worldwide)<br>Thick 14 AWG wire gauge manages high power levels required for larger equipment |
| PLUG COLOR                  | Black                                                                                                                                                                                                                                                                                                                                                                    |

|                  |                            |
|------------------|----------------------------|
| SIDEA CONNECTOR1 | IEC-320-C14                |
| SIDEB CONNECTOR1 | IEC-320-C15                |
| VOLTAGE RATING   | 100 - 250 VAC              |
| CONNECTOR GROUP  | C15<br>C13                 |
| CONNECTOR        | IEC 320-C14<br>IEC 320-C15 |

|       |
|-------|
|       |
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |



□□□□ Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

□□□□□□□□□□□□□□□□□□□□□□□□

