

# Eaton OSD100M160

Eaton Bussmann series low voltage british standard fuse, 100 A, AC 415 V, 26 x 95 mm, gM, 100M160

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	OSD100M160
UPC	051712844420
PRODUCT LENGTH/DEPTH	95 mm
PRODUCT HEIGHT	26 mm
PRODUCT WIDTH	26 mm
PRODUCT WEIGHT	82 g
COMPLIANCES	RoHS Compliant

<b>AMPERAGE RATING</b>	100 A
<b>FITTED WITH:</b>	Offset bolted tags
<b>CURRENT TYPE</b>	AC
<b>MOUNTING DIMENSION</b>	M5
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	73 mm
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>MOTOR CURRENT RATING</b>	100M160
<b>RATED VOLTAGE AC</b>	415 V
<b>CLASS</b>	Class gM
<b>FUSE TYPE</b>	OSD
<b>UTILIZATION CATEGORY</b>	gM (motor protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	5 W
<b>CONNECTION</b>	73 mm fixing centre
<b>CONSTRUCTION</b>	BS88
<b>CONSTRUCTION SIZE</b>	Other
<b>FUSE SHAPE</b>	Offset bolted tags
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	CM100F Red spot fuse holder SC100 Safeclip fuse holder
<b>VOLTAGE RATING</b>	415 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250977en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

