



## Eaton P571-006-MINI

High-Speed HDMI to Mini HDMI Cable with Ethernet (M/M), 6 ft.

□□□□

|                             |                               |
|-----------------------------|-------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Tripp Lite series cable |
| <b>CATALOG NUMBER</b>       | P571-006-MINI                 |
| <b>UPC</b>                  | 037332175601                  |
| <b>PRODUCT LENGTH/DEPTH</b> | 7 in                          |
| <b>PRODUCT HEIGHT</b>       | 0.25 in                       |
| <b>PRODUCT WIDTH</b>        | 7 in                          |
| <b>PRODUCT WEIGHT</b>       | 0.1 lb                        |
| <b>WARRANTY</b>             | Limited lifetime              |
| <b>COMPLIANCES</b>          | REACH<br>RoHS                 |

| □□□□                     |                                                                                                                                                                                                                                      |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TYPE                     | Passive Cable                                                                                                                                                                                                                        |
| AUDIO SPECIFICATION      | Stereo Audio                                                                                                                                                                                                                         |
| OPERATING HUMIDITY RANGE | 30% to 90% RH, Non-Condensing                                                                                                                                                                                                        |
| STORAGE HUMIDITY RANGE   | 30% to 90% RH, Non-Condensing                                                                                                                                                                                                        |
| COLOR                    | Black                                                                                                                                                                                                                                |
| CABLE JACKET RATING      | VW-1                                                                                                                                                                                                                                 |
| CABLE JACKET COLOR       | Black                                                                                                                                                                                                                                |
| CONNECTOR COLOR          | Black                                                                                                                                                                                                                                |
| CONNECTOR PLATING        | Nickel                                                                                                                                                                                                                               |
| CONNECTOR TYPE           | Video                                                                                                                                                                                                                                |
| PRODUCT FEATURES         | Ethernet Support<br>3D Video Supported<br>Consumer Electronics Control (CEC) Supported<br>EDID Support                                                                                                                               |
| CABLE JACKET MATERIAL    | PVC                                                                                                                                                                                                                                  |
| COLOR DEPTH              | 48-bit Deep color                                                                                                                                                                                                                    |
| CONNECTOR STYLE          | Straight                                                                                                                                                                                                                             |
| PACKAGE CONTENTS         | High Speed with Ethernet<br>HDMI to Mini-HDMI Cable,<br>6 ft.                                                                                                                                                                        |
| PRODUCT HIGHLIGHTS       | Supports UHD resolutions up to 4K (4:4:4) for crystal-clear video<br>24K gold-plated connectors for maximum conductivity<br>Lifetime limited warranty (Worldwide)<br>Premium foil and braid shielding protects against EMI/RFI noise |
| CONTACT PLATING          | Gold                                                                                                                                                                                                                                 |
| CHROMA SUB SAMPLING      | 4:2:2<br>4:4:4                                                                                                                                                                                                                       |
| SIDEA CONNECTOR1         | MINI HDMI (MALE)                                                                                                                                                                                                                     |
| SIDEB CONNECTOR1         | HDMI (MALE)                                                                                                                                                                                                                          |
| SIDEB CONNECTOR3         | HDMI (MALE)                                                                                                                                                                                                                          |
| TECHNOLOGY               | HDMI                                                                                                                                                                                                                                 |
| CONNECTOR GROUP          | HDMI<br>Mini HDMI                                                                                                                                                                                                                    |
| CONNECTOR                | HDMI (male)<br>Mini HDMI (male)                                                                                                                                                                                                      |
| CABLE LENGTH             | 6 Foot                                                                                                                                                                                                                               |
| MAX SUPPORTED VIDEO      | 3840 x 2160 (4K) @ 30Hz                                                                                                                                                                                                              |

| □□ |  |
|----|--|
|----|--|

|                             |                             |
|-----------------------------|-----------------------------|
| RESOLUTION                  |                             |
| MINIMUM BEND RADIUS         | 60mm                        |
| LED INDICATORS              | 0                           |
| OPERATING TEMPERATURE RANGE | 32° to 140°F (0° to 60°C)   |
| STORAGE TEMPERATURE RANGE   | -4° to 140°F (-20° to 60°C) |
| CABLE TYPE                  | Passive                     |
| SIGNAL TRANSMISSION         | Bidirectional               |
| MAX RESOLUTION              | 4K/30                       |
| CABLE LENGTH RANGE          | 5 - 8ft (1 - 2M)            |

|  |
|--|
|  |
|  |
|  |
|  |



  Eaton House  
30 Pembroke Road  
Dublin 4,     
Eaton.com

