



□□□□□

## Eaton PDG23M0060P3MJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 60A, 65kA/480V, PXR25 LSIG w/ Modbus RTU and Relays, Standard Line and Load (PDG2X3T100)

□□□□

|                             |                                                 |
|-----------------------------|-------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Power Defense molded case circuit breaker |
| <b>CATALOG NUMBER</b>       | PDG23M0060P3MJ                                  |
| <b>UPC</b>                  | 786679239377                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 88.9 mm                                         |
| <b>PRODUCT HEIGHT</b>       | 152.4 mm                                        |
| <b>PRODUCT WIDTH</b>        | 104.6 mm                                        |
| <b>PRODUCT WEIGHT</b>       | 1.82 kg                                         |
| <b>COMPLIANCES</b>          | RoHS Compliant                                  |
| <b>CERTIFICATIONS</b>       | UL 489<br>CCC Marked<br>IEC 60947-2<br>CSA      |

|                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AMPERAGE RATING                          | 60 A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| VOLTAGE RATING                           | 600 Vac                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| TRIP TYPE                                | T293                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| CIRCUIT BREAKER TYPE                     | PD2 Global                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| CIRCUIT BREAKER FRAME TYPE               | Complete breaker                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| TERMINALS                                | Standard Line and Load                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| FRAME                                    | 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| CLASS                                    | Class A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| COMMUNICATION                            | Modbus RTU                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| INTERRUPT RATING                         | 65 kAIC at 480 Vac                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| SWITCH OFF TECHNIQUE                     | Electronic                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| VOLTAGE RATING - MAX                     | 600 V                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| INTERRUPT RATING RANGE                   | 70 kAIC Icu/ 53 kAIC Ics/<br>154 kAIC Icm @380-415V (IEC)<br>50 kAIC Icu/ 40 kAIC Ics/<br>105 kAIC Icm @440V (IEC)<br>35 kAIC @600V (UL/CSA)<br>50 kAIC Icu/ 30 kAIC Ics/<br>105 kAIC Icm @480V Brazil (IEC)<br>100 kAIC @240V (UL)<br>10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)<br>100 kAIC Icu/ 100 kAIC Ics/<br>220 kAIC Icm @240V (IEC)<br>65 kAIC @480V (UL)<br>22 kAIC Icu @250 Vdc<br>30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)<br>22 kAIC Icu @125 Vdc<br>25 kAIC @600V (UL/CSA) |
| NUMBER OF POLES                          | Three-pole                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| SPECIAL FEATURES                         | Modbus / relays                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

