



□□□□□

## Eaton PLLA2-UNV1-M2

Eaton Crouse-Hinds series Champ Pro PLLA linear LED light fixture, Cool white, 3/4" entries, Natural alum finish, 2 ft, Glass lens, 4000 lumens, 132 lm/W, Copper-free alum, Flush ceiling mount, Wide, >0.92 PF, 120-277 Vac, 127/250 Vdc, 30W

□□□□

|                             |                                                                   |
|-----------------------------|-------------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Champ Pro PLLA linear LED light fixture |
| <b>CATALOG NUMBER</b>       | PLLA2-UNV1-M2                                                     |
| <b>UPC</b>                  | 786689651152                                                      |
| <b>PRODUCT LENGTH/DEPTH</b> | 25.94 in                                                          |
| <b>PRODUCT HEIGHT</b>       | 4.42 in                                                           |
| <b>PRODUCT WIDTH</b>        | 7.13 in                                                           |
| <b>PRODUCT WEIGHT</b>       | 15.1 lb                                                           |

## Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous Locations

**STANDARDS TYPE** NEC/CEC

**NEMA RATING** 4X

**INGRESS PROTECTION (IP) RATINGS** IP66  
IP67

## Product specifications

**LAMP TYPE** LED

**COLOR TEMPERATURE** Cool white

**LAMP LENGTH** 2 ft

**LUMENS** 4000

**LUMENS PER WATT** 132

**OPTICAL DISTRIBUTION** Wide

**MOUNTING METHOD** Flush ceiling

**VOLTAGE RATING** 120-277 Vac, 127/250 Vdc

**FREQUENCY RATING** 50/60 Hz

**LENS MATERIAL** Glass

**ENTRY SIZE** 3/4"

**FINISH** Natural aluminum

**MATERIAL** Copper-free aluminum

**WATTAGE** 30W

**POWER FACTOR** > 0.92

|          |                                                                                                                                                                                             |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|          | <a href="#">IF 1938 - Champ Pro Linear PLLA M2 LED Fixtures</a>                                                                                                                             |
| 00000    | <a href="#">IF 1941 - Champ Linear PLLA M2 LED Light Engine Fixtures</a>                                                                                                                    |
|          | <a href="#">IF 1948 - PLLA-M2 Linear LED with Emergency Battery Back-up</a>                                                                                                                 |
| 00000000 | <a href="#">Eaton Specification Sheet - PLLA2-UNV1-M2</a><br><a href="#">Champ Pro PLLA LED Industrial Linear</a>                                                                           |
|          | <a href="#">Crouse-Hinds series Champ PLLA LED Linear brochure</a>                                                                                                                          |
| 0000     | <a href="#">Crouse-Hinds series industrial LED lighting solutions</a><br><a href="#">Crouse-Hinds series Global LED lighting portfolio</a>                                                  |
| 0000     | <a href="#">Crouse-Hinds series Champ Pro PLLA LED Linear catalog page</a>                                                                                                                  |
|          | <a href="#">Champ Pro PLLA Industrial Linear LED Light Fixtures UL certification</a>                                                                                                        |
| 0000     | <a href="#">Champ Pro PLLA Industrial Linear LED Light Fixtures Canadian certification</a><br><a href="#">Champ Pro PLLA Industrial Linear LED Light Fixtures UL certification (Marine)</a> |

