



## Eaton U209-000-R

USB-A to RS232 (DB9) Serial Adapter Cable -  
(M/M), 5 ft. (1.52 m)

□□□□

|                             |                                             |
|-----------------------------|---------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Tripp Lite series USB adapter         |
| <b>CATALOG NUMBER</b>       | U209-000-R                                  |
| <b>UPC</b>                  | 037332095640                                |
| <b>PRODUCT LENGTH/DEPTH</b> | 4.7 in                                      |
| <b>PRODUCT HEIGHT</b>       | 1 in                                        |
| <b>PRODUCT WIDTH</b>        | 4.1 in                                      |
| <b>PRODUCT WEIGHT</b>       | 0.001 lb                                    |
| <b>WARRANTY</b>             | 3 year limited                              |
| <b>COMPLIANCES</b>          | RoHS<br>CE Marked<br>REACH<br>FCC Compliant |
| <b>CERTIFICATIONS</b>       | EN 55024<br>EN 55032                        |

|                             |                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| □□□□                        |                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| RELATIVE HUMIDITY           | 0-80% non-condensing                                                                                                                                                                                                                                                                                                                                                                                                               |
| COLOR                       | Black                                                                                                                                                                                                                                                                                                                                                                                                                              |
| CABLE JACKET COLOR          | Black                                                                                                                                                                                                                                                                                                                                                                                                                              |
| CONNECTOR PLATING           | Gold                                                                                                                                                                                                                                                                                                                                                                                                                               |
| CONNECTOR TYPE              | USB/Thunderbolt/Lightning                                                                                                                                                                                                                                                                                                                                                                                                          |
|                             | Serial/parallel                                                                                                                                                                                                                                                                                                                                                                                                                    |
| USB SPECIFICATION           | USB 2.0 (up to 480 Mbps)                                                                                                                                                                                                                                                                                                                                                                                                           |
| CABLE JACKET MATERIAL       | PVC                                                                                                                                                                                                                                                                                                                                                                                                                                |
| PACKAGE CONTENTS            | USB-A to RS-232 (DB9)<br>Serial Adapter Cable, M/M,<br>5 ft. (1.5 m)<br>Owner's manual                                                                                                                                                                                                                                                                                                                                             |
| PRODUCT HIGHLIGHTS          | Portable design fits comfortably inside a backpack or laptop bag<br>Plug-and-play with no external power required for easy, immediate installation<br>Premium double-shielded cable eliminates crosstalk and reduces EMI/RFI line noise<br>Compatible with Windows, macOS and Linux operating systems<br>Supports data transfer rates up to 250 Kbps-2x the speed of a built-in serial port<br>3-year limited warranty (Worldwide) |
| SIDEA CONNECTOR1            | USB A (MALE)                                                                                                                                                                                                                                                                                                                                                                                                                       |
| SIDEB CONNECTOR1            | DB9 (MALE)                                                                                                                                                                                                                                                                                                                                                                                                                         |
| OPERATING TEMPERATURE       | 32° to 140°F (0° to 60°C)                                                                                                                                                                                                                                                                                                                                                                                                          |
| OPERATING TEMPERATURE RANGE | 32° to 140°F (0° to 60°C)                                                                                                                                                                                                                                                                                                                                                                                                          |
| STORAGE TEMPERATURE RANGE   | -4° to 176°F (-20° to 80°C)                                                                                                                                                                                                                                                                                                                                                                                                        |
| SIDEB CONNECTOR3            | DB9 (MALE)                                                                                                                                                                                                                                                                                                                                                                                                                         |
| HOST CONNECTOR              | USB A (MALE)                                                                                                                                                                                                                                                                                                                                                                                                                       |
| TECHNOLOGY                  | Serial<br>USB                                                                                                                                                                                                                                                                                                                                                                                                                      |
| CABLE LENGTH                | 5 - 8ft (1 - 2M)                                                                                                                                                                                                                                                                                                                                                                                                                   |
| NUMBER OF PORTS             | 1                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| CABLE OUTER DIAMETER        | 5.0 +/- 0.15                                                                                                                                                                                                                                                                                                                                                                                                                       |

|    |
|----|
| □□ |
|----|

|                    |                            |
|--------------------|----------------------------|
| (OD)               |                            |
| CONNECTOR GROUP    | USB-A<br>DB9               |
| MATERIAL           | PVC                        |
| CABLE LENGTH RANGE | 5 - 8ft (1 - 2M)           |
| CONNECTOR          | USB A (male)<br>DB9 (male) |

|  |
|--|
|  |
|  |
|  |
|  |



  Eaton House  
30 Pembroke Road  
Dublin 4,     
Eaton.com

