




Eaton U280-W02-A1C1

Dual-Port USB Wall Charger with PD Charging - USB-C (39W) & USB-A (5V 2.4A/12W)

□□□□

PRODUCT NAME	Eaton Tripp Lite series multi-device charger
CATALOG NUMBER	U280-W02-A1C1
UPC	037332214416
PRODUCT LENGTH/DEPTH	5.35 in
PRODUCT HEIGHT	1.46 in
PRODUCT WIDTH	5.51 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS REACH FCC Compliant
CERTIFICATIONS	UL Listed

□□□□	
TYPE	Wall Charger
CHARGING PORTS DETAILS	USB-C: 39W USB-A: 5V 2.5A (12W)
NUMBER OF CHARGING PORTS	2
TOTAL CHARGING AMPS	1.5A
TOTAL CHARGING WATTS	51
NUMBER OF PORTS	2
OVER CURRENT PROTECTION	Yes
OVERLOAD PROTECTION	Yes
CHARGING METHOD DETAIL	Power Deliver 2.0; Quick Charge 2.0
INPUT CONNECTION TYPE	NEMA 1-15P
INPUT CURRENT	1.5A
INPUT FREQUENCY	50 / 60 Hz
OPERATING TEMPERATURE RANGE	32° to 95°F (0° to 35°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
OPERATING HUMIDITY RANGE	30 TO 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	10 TO 90% RH, Non-Condensing
COLOR	Black
INPUT PLUG TYPE	NEMA 1-15P (NON-POLARIZED)
MATERIAL	Plastic
CHARGING PORTS / AMPS	2.4A 3A / 2.6A
CHARGING METHOD	USB
CONNECTOR TYPE	Power USB/Thunderbolt/Lightning
INPUT NOMINAL VOLTAGE	230 VAC 120 VAC
PRODUCT FEATURES	Overvoltage Protection NEMA 1-15P Overcurrent Protection
PACKAGE CONTENTS	U280-W02-A1C1 Dual-Port USB Wall Charger with PD Charging
PRODUCT HIGHLIGHTS	Ideal for charging smartphones, tablets, e- readers and MP3 players while traveling



	Maximum charging power output of 51W: 39W USB-C and 12W USB-A Auto-sensing USB-A port adjusts charging power level to your device up to 5V 2.4A 2-year limited warranty (Worldwide) Plug folds inward to protect it from damage and help the unit fit into a purse or bag USB-C PD Charging port supports Quick Charge 2.0 Class A 5/9/12V technology
CHARGING FORM FACTOR	Direct plug-in
CHARGING PORT TYPE	USB C (FEMALE) USB A (FEMALE)
PACKAGING TYPE	Box
SIDEA CONNECTOR1	NEMA 1-15P (NON-POLARIZED)
SIDEB CONNECTOR1	USB A (FEMALE) USB C (FEMALE)
SIDEB CONNECTOR3	USB A (FEMALE) USB C (FEMALE)
DEVICE COMPATIBILITY	Laptop Phone Amazon Kindle Chromebook Tablet
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
CONNECTOR GROUP	USB-A 1-15P
CONNECTOR	USB A (female) NEMA 1-15P (non-polarized)

