



Eaton U330F-30M-G1

USB 3.2 Gen 1 CL3-Rated Fiber Active Optical Cable (AOC) - Extension/Repeater, A M/F, Black, 30 m

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U330F-30M-G1
UPC	037332260390
PRODUCT LENGTH/DEPTH	9.25 in
PRODUCT HEIGHT	2.56 in
PRODUCT WIDTH	9.65 in
PRODUCT WEIGHT	2.21 lb
COMPLIANCES	FCC Compliant RoHS CE Marked REACH
CERTIFICATIONS	ICES NOM

APPLICATION

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 30 meters to more easily place a device
- Provide a high-quality replacement for a worn-out or missing extension cable

OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% TO 90% RH, Non-Condensing
CABLE JACKET RATING	CL3
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Light gray
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	Bus Powered
USB SPECIFICATION	USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	<p>CL3-rated PVC cable jacket meets required standards for commercial in-wall installation</p> <p>Slim, flexible cable easily installs around corners and through hard-to-reach areas</p> <p>Fiber optic construction ideal for long-distance connections not supported by copper</p> <p>Adds 30 m (98 ft.) to your existing connection to provide flexibility in placing devices</p> <p>Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers</p>
CONTACT PLATING	Gold

POWER SOURCE TYPE	USB
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB A (FEMALE)
SIDEB CONNECTOR2	MICRO-USB B (FEMALE)
OPERATING TEMPERATURE	32° to 113°F (0° to 45°C)
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
SIDEB CONNECTOR3	USB A (FEMALE)
TECHNOLOGY	USB 3.x
DATA TRANSFER RATE	5 Gbps
CABLE LENGTH	98.4 Foot
CABLE OUTER DIAMETER (OD)	4.6mm
CABLE TYPE	Active
MATERIAL	PVC + Zinc Alloy
WIRE GAUGE (AWG)	24
CABLE LENGTH RANGE	50ft and up (15M and up)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

