



Eaton U444-06N-H4K6WC

USB-C to HDMI Adapter (M/F) - 4K 60 Hz, 60W PD Charging, HDCP 2.2, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series adapter
CATALOG NUMBER	U444-06N-H4K6WC
UPC	037332210739
PRODUCT LENGTH/DEPTH	1.57 in
PRODUCT HEIGHT	0.45 in
PRODUCT WIDTH	1.69 in
PRODUCT WEIGHT	0.0672 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS CE Marked FCC Compliant

□□□□	
□□	
APPLICATION	• Play video from your MacBook or Chromebook on a large-screen HDTV • Give a video presentation at a meeting, training session or conference • Write and edit multiple documents on a bigger monitor • Stream 4K video for digital signage at a trade show • Charge and power a USB-C or Thunderbolt 3 device
TYPE	USB Multiport Adapter
AUDIO SPECIFICATION	7.1 Channel Surround Sound
OPERATING HUMIDITY RANGE	10% to 85% RH
STORAGE HUMIDITY RANGE	5% to 90% RH
COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
	Networking-fiber
PRODUCT FEATURES	Extended Mode Mirror Mode 3D Video Supported Bus Powered DisplayPort Alt Mode
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
PACKAGE CONTENTS	Owner's manual U444-06N-H4K6WC USB-C 3.1 to HDMI 4K Adapter, M/F, White
PRODUCT HIGHLIGHTS	Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video 3-year limited warranty (Worldwide) Reversible USB-C plug connects in either direction

	for immediate no-fuss use Transmits video signals from sources supporting USB-C DisplayPort Alt Mode USB-C PD 3.0 port supports 20V 3A (60W) power output for charging host device Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
OPERATING TEMPERATURE	32° to 113°F (0° to 45°C)
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
DATA PORTS	USB C (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
HOST CONNECTOR	USB C (MALE)
TECHNOLOGY	HDMI
VIDEO PORTS DETAILS	• HDMI 2.0 • HDCP 2.2
NUMBER OF DISPLAYS	1
NUMBER OF MONITORS SUPPORTED	1
NUMBER OF USB HUB PORTS	0
CONNECTOR GROUP	USB-C HDMI
MATERIAL	PVC
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K x 2K) @ 60Hz
CONNECTOR	USB C (male) HDMI (female)
SUPPORTED RESOLUTION	1280x720 (720p) 1920x1080 (1080p) 3840x2160 (4K)
VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI (FEMALE) HDMI 2.0 HDCP 2.2

