




Eaton U460-004-4C-G2C

4 Port USB-C Hub with 100W PD charging,
USB 3.2 Gen 2 (10Gbps), Portable, Gray

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U460-004-4C-G2C
UPC	037332286109
PRODUCT LENGTH/DEPTH	3.78 in
PRODUCT HEIGHT	0.47 in
PRODUCT WIDTH	1.57 in
PRODUCT WEIGHT	0.14 lb
COMPLIANCES	RoHS3 CE Marked REACH FCC Compliant UKCA

□□□□	
TYPE	Hub
NUMBER OF CHARGING PORTS	4
TOTAL CHARGING WATTS	100
DEVICE COMPATIBILITY	Amazon Kindle Computer Headphones Video Game System Tablet Chromebook Laptop Phone Watch
OPERATING HUMIDITY RANGE	10% TO 85% RH, NON-CONDESNING
STORAGE HUMIDITY RANGE	25% TO 93% RH, NON-CONDESNING
COLOR	Black Gray
MATERIAL	TPE + ABS
USB HUB PORTS	Yes
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CABLE JACKET COLOR	Black
CHARGING PORTS / AMPS	1.5A 5A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	USB Charging Bus Powered Battery Charging (5V/1.5A Port)
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
CABLE JACKET MATERIAL	TPE
PACKAGE CONTENTS	U460-004-4C-G2C 4-Port USB-C Hub, Gray Installation instructions
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software required for easy, immediate installation 3 ports support 5V 1.5A (7.5W) fast-charging for headsets and other small devices Travel-sized USB-C hub features 4 USB-C ports for connecting essential peripherals Power Delivery port supports 20V 5A (100W)



	power output for charging host device 3-year limited warranty (Worldwide) All ports support USB 3.2 Gen 2 speeds up to 10 Gbps for fast data transfers
CHARGING PORT TYPE	USB C (FEMALE)
PACKAGING TYPE	Box
PLUG COLOR	White Blue
POWER SOURCE TYPE	USB Bus
SIDEA CONNECTOR1	USB C (MALE)
COMPATIBLE DEVICES	Tablet Chromebook Smartphone Laptop Portable Speaker Video Game Console
SIDEB CONNECTOR1	USB C (FEMALE)
DATA PORTS	USB-C - USB 3.2 Gen 2 (10 Gbps) USB C (FEMALE)
SIDEB CONNECTOR3	USB C (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	1.5 A 5 A 5A
TECHNOLOGY	Thunderbolt USB 3.x
CHARGING PORTS	USB-C: 100W (20V 5A) Power Delivery (PD 3.0) USB-C: 5V 1.5A (7.5W)
DATA TRANSFER RATE	10 Gbps
NUMBER OF PORTS	4
NUMBER OF USB HUB PORTS	4
TOTAL NUMBER OF PORTS	4
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	14° to 176°F (-10° to 80°C)
OVER CURRENT PROTECTION	Y
DATA PORTS DETAILS	USB-C - USB 3.2 Gen 2 (10 Gbps)
USB POWER DELIVERY (PD) CHARGING	3

SPECIFICATION

□□□□:

□□□□:

□□□:

□□:



Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
Eaton.com

© 2026 〇〇 〇〇〇〇〇〇〇〇

□□□□□□□□□□□□□□□□□□□□□□

