



Eaton U280-001-C2

USB Tablet / Phone Car Charger, 5V 2.4A / 12W

□□□□

PRODUCT NAME	Eaton Tripp Lite series car charger
CATALOG NUMBER	U280-001-C2
UPC	037332184276
PRODUCT LENGTH/DEPTH	6.1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	4.1 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS CE Marked REACH WEEE Directive FCC Compliant



Powering Business Worldwide

□□□□	
TYPE	Car Charger
CHARGING PORTS DETAILS	USB-A: 5V 2.4A (12W)
NUMBER OF CHARGING PORTS	1
TOTAL CHARGING AMPS	1.4A
TOTAL CHARGING WATTS	12
NUMBER OF PORTS	1
OUTPUT CAPACITY	12 W
OVERLOAD PROTECTION	Yes
INPUT CONNECTION TYPE	Automatic Vehicle Cigarette Lighter
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	-40° to 176°F (-40° to 80°C)
OPERATING HUMIDITY RANGE	20 to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5 to 95% RH, Non-Condensing
COLOR	White
INPUT PLUG TYPE	Car auxiliary power outlet
CHARGING PORTS / AMPS	2.4A
CHARGING METHOD	USB
CONNECTOR TYPE	USB/Thunderbolt/Lightning
INPUT NOMINAL VOLTAGE	12 VDC
PRODUCT FEATURES	Overcurrent Protection Overvoltage Protection Automatic Vehicle Cigarette Lighter
PACKAGE CONTENTS	2.4A Single USB Car Charger
PRODUCT HIGHLIGHTS	Quickly charges a Tablet or Phone with up to 2.4A of power 5V 2.4A USB port 2-year limited warranty (Worldwide)
CHARGING FORM FACTOR	Direct plug-in
CHARGING PORT TYPE	USB A (FEMALE)
SIDEA CONNECTOR1	Car Cigarette Lighter
COMPATIBLE DEVICES	Tablet Smartphone

	Laptop
SIDE B CONNECTOR1	USB A (FEMALE)
SIDE B CONNECTOR3	USB A (FEMALE)
DEVICE COMPATIBILITY	Phone Amazon Kindle Tablet
TECHNOLOGY	USB
CONNECTOR GROUP	USB-A
CONNECTOR	USB A (female)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

