



Eaton U338-CF-SATA-5G

USB 3.1 Gen 1 (5 Gbps) to CFast 2.0 Card
and SATA III Adapter, USB-A

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U338-CF-SATA-5G
UPC	037332222091
PRODUCT LENGTH/DEPTH	4.4 in
PRODUCT HEIGHT	1.125 in
PRODUCT WIDTH	3.6 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	CE Marked REACH RoHS FCC Compliant

APPLICATION

- Transfer high-definition video and image files between a digital camera or camcorder and your computer or laptop
- Load a file onto a SATA drive or CFast memory card at the office for presenting on a different computer elsewhere
- Temporarily store data that cannot be emailed to another computer or uploaded to cloud storage

AUDIO SPECIFICATION	No
RELATIVE HUMIDITY	0-80% non-condensing
COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning Storage
PRODUCT FEATURES	UASP Support Bus Powered
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps)
PACKAGE CONTENTS	U338-CF-SATA-5G USB 3.1 Gen 1 (5 Gbps) to CFast 2.0 Card and SATA III Adapter, USB-A Owner's manual
PRODUCT HIGHLIGHTS	Ideal for photographers and videographers who need to upload large files quickly Easy installation with plug-and-play operation—no software or drivers required Compatible with 2.5 in. SATA I, II and III HDDs and SSDs up to 2 TB Works with all major operating systems, including Windows, Mac and Linux Supports USB 3.1 Gen 1

	speeds up to 5 Gbps to ensure fast data transfers 3-year limited warranty (Worldwide)
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	22 PIN SATA + POWER (FEMALE) CF (Male)
OPERATING TEMPERATURE	32° to 167°F (0° to 75°C)
OPERATING TEMPERATURE RANGE	32° to 167°F (0° to 75°C)
STORAGE TEMPERATURE RANGE	14° to 176°F (-10° to 80°C)
SIDEB CONNECTOR3	22 PIN SATA + POWER (FEMALE) CF (Male)
TECHNOLOGY	SATA / eSATA SATA/eSATA
BUILT-IN CABLE LENGTH	0.39 ft
CABLE LENGTH	Up to 4ft (up to 1M)
NUMBER OF PORTS	2
LED INDICATORS	Blue (CFast Card connection), Red (SATA connection), Blue/Red (CFast/SATA connection)
CONNECTOR GROUP	USB-A SATA
MATERIAL	ABS
CONNECTOR	22-pin SATA+ power (female) USB 3.0 A (male)

□□□□:
□□□□:
□□□:
□□: