




Eaton U428-003

USB-C to USB-A Cable (M/M), USB 3.2 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U428-003
UPC	037332189288
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.12 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH FCC Compliant CE Marked

□□□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U428-003 USB 3.2 Gen 1 (5 Gbps) Cable, USB Type-C (USB-C) to USB Type-A M/M, 3-ft. (0.91 m)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Works with USB 3.0 devices
	Features reversible USB Type-C male plug on one end Connects a USB Type-C (USB-C) device to the USB Type-A port on your tablet, computer, or USB charger Supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB 3.0 A (MALE) USB A (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB A (MALE)
TECHNOLOGY	Thunderbolt USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	4.5MM
CABLE TYPE	Passive



CONNECTOR GROUP	USB-A USB-C
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB 3.0 A (male) USB A (male) USB C (male)
