



Eaton U436-06N-G-C

USB-C to Gigabit Network Adapter with USB-C PD Charging - Thunderbolt 3, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series network adapter
CATALOG NUMBER	U436-06N-G-C
UPC	037332193827
PRODUCT LENGTH/DEPTH	4.8 in
PRODUCT HEIGHT	0.7 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS FCC Compliant REACH CE Marked
CERTIFICATIONS	EN 55032 EN 55035



Powering Business Worldwide

□□□□	
RELATIVE HUMIDITY	5% to 90% RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3
CHARGING METHOD	USB
CONNECTOR TYPE	USB/Thunderbolt/Lightning
	Networking-copper
PRODUCT FEATURES	Suspend Mode Support Bus Powered Full Duplex Support Remote Wakeup Support Auto MDIX Support
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
NETWORK SPEED	1 Gbps (Gigabit)
PACKAGE CONTENTS	U436-06N-G-C USB 3.1 Gen 1 USB-C to Gigabit Ethernet NIC Network Adapter Owner's manual
PRODUCT HIGHLIGHTS	Plug-and-play—no software or drivers required LEDs indicate activity and link Compatible with Windows, Mac and Chromium USB-C 60W Power Delivery port connects to wall charger to power device 3-year limited warranty (Worldwide) Supports true 10/100/1000 Mbps network speeds Connects a USB Type-C or Thunderbolt™ 3 device to a wired Ethernet network
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB C (FEMALE)
SIDEB CONNECTOR2	RJ45 (FEMALE)
OPERATING TEMPERATURE	32° to 158°F (0° to 70°C)

OPERATING TEMPERATURE RANGE	32° to 158°F (0° to 70°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
SIDEB CONNECTOR3	USB C (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	3 A
TECHNOLOGY	Cat5/5e Cat6
NETWORK COMPATIBILITY	1 Gbps (Gigabit)
CHARGING PORTS	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
NUMBER OF CHARGING PORTS	1
NUMBER OF PORTS	2
NUMBER OF USB HUB PORTS	0
POWER CONSUMPTION (WATTS)	0.9 W
BTUS	3.1 BTU/Hr
CABLE OUTER DIAMETER (OD)	3.9mm
LED INDICATORS	Green (Power), Orange (Activity)
CONNECTOR GROUP	USB-C RJ45
MATERIAL	ABS, PVC
RECOMMENDED CATEGORY CABLE	Cat5/Cat5e/Cat6 Cables
POWER PROVIDED TO CONNECTED DEVICE(S)	Up to 20V 3A (60W) Input (USB-C)
TOTAL CHARGING WATTS	60 W
CONNECTOR	RJ45 (female) USB C (male)
NETWORK PORTS	RJ45 (FEMALE)

