



Eaton U460-004-4A-G2

4-Port USB Hub - USB 3.1 Gen 2, 10 Gbps, 4 USB-A Ports, Thunderbolt 3, Aluminum Housing

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U460-004-4A-G2
UPC	037332218247
PRODUCT LENGTH/DEPTH	3.15 in
PRODUCT HEIGHT	0.79 in
PRODUCT WIDTH	5.91 in
PRODUCT WEIGHT	0.093 lb
WARRANTY	3 year limited
COMPLIANCES	CE Marked RoHS REACH FCC Compliant

APPLICATION

- Connect up to 4 USB peripherals, such as an external hard drive, smartphone, power meter and printer
- Transfer files quickly to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Download photos from a digital camera

TYPE	Hub
RELATIVE HUMIDITY	0-90% non-condensing
COLOR	Black
MATERIAL	Aluminum, PVC
USB HUB PORTS	Yes
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	USB Charging Bus Powered
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
PACKAGE CONTENTS	U460-004-4A-G2 USB 3.2 C Hub, 10 Gbps, Aluminum Housing

PRODUCT HIGHLIGHTS

Plug-and-play operation with no software required for easy, immediate installation
USB-C 3.2 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
Reversible USB-C plug connects in either direction for immediate no-fuss use
Supports USB 3.2 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
3-year limited warranty (Worldwide)
Accepts up to 4 USB peripherals, turning your

	laptop into a mini workstation
PACKAGING TYPE	Box
PLUG COLOR	Blue White
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB A (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 2 (10 Gbps) USB A (FEMALE)
SIDEB CONNECTOR3	USB A (FEMALE)
HOST CONNECTOR	USB C (MALE)
TECHNOLOGY	USB 3.x
FEATURES	Flex Center
NUMBER OF PORTS	4
NUMBER OF USB HUB PORTS	4
NUMBER OF MONITORS SUPPORTED	0
STORAGE TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 2 (10 Gbps)

□□□□:
□□□□:
□□□:
□□: