



Eaton UR024-003-WH

Universal Reversible USB 2.0 Extension Cable (Reversible A to A M/F), White, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	UR024-003-WH
UPC	037332182067
PRODUCT LENGTH/DEPTH	6.3 in
PRODUCT HEIGHT	0.1 in
PRODUCT WIDTH	5.9 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS



Powering Business Worldwide



OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	White
CONNECTOR TYPE	USB/Thunderbolt/Lightning
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	Universal Reversible USB 2.0 A-Male to A-Female Extension Cable - White - 3-ft. (0.91 m)

PRODUCT HIGHLIGHTS	Gold plated contacts provide superior conductivity Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications Universal / Reversible A-Male plugs in any direction Extend distances of USB 2.0 cables with this extension cable Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
---------------------------	--

SIDEA CONNECTOR1	REVERSIBLE USB A (MALE)
-------------------------	-------------------------

SIDEB CONNECTOR1	USB A (FEMALE)
-------------------------	----------------

OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
------------------------------	-----------------------------

OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
------------------------------------	-----------------------------

STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
----------------------------------	----------------------------

SIDEB CONNECTOR3	USB A (FEMALE)
-------------------------	----------------

TECHNOLOGY	USB 2.0 (High Speed)
-------------------	----------------------

CABLE LENGTH	Up to 4ft (up to 1M)
---------------------	----------------------

CABLE TYPE	Passive
-------------------	---------

CONNECTOR GROUP	USB-A
------------------------	-------

CABLE LENGTH RANGE	Up to 4ft (up to 1M)
---------------------------	----------------------

CONNECTOR	USB A reversible (male) USB A (female)
------------------	---



