



Eaton UR050-001-24G

Universal Reversible USB 2.0 Cable,
28/24AWG (Reversible A to 5Pin Micro B
M/M), 1 ft. (0.31 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	UR050-001-24G
UPC	037332186140
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.083 lb
COMPLIANCES	RoHS



Powering Business Worldwide



OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR TYPE	USB/Thunderbolt/Lightning
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	1-ft. (0.31 m) USB2.0 Universal / Reversible A to Micro-USB B Device Cable, 28/24AWG (A Male to Micro-B Male)

PRODUCT HIGHLIGHTS	<p>Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines</p> <p>Universal / Reversible "A" Male to Micro-B Male</p> <p>Supports USB 2.0 data transfer rates up to 480Mbps</p> <p>Double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines</p> <p>Constructed of 24AWG power lines for charging higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge</p>
---------------------------	---

SIDEA CONNECTOR1	REVERSIBLE USB A (MALE)
-------------------------	-------------------------

SIDEB CONNECTOR1	MICRO-USB B (MALE)
-------------------------	--------------------

OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
------------------------------	-----------------------------

OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
------------------------------------	-----------------------------

STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
----------------------------------	----------------------------

SIDEB CONNECTOR3	MICRO-USB B (MALE)
-------------------------	--------------------

TECHNOLOGY	USB 2.0 (High Speed)
-------------------	----------------------

CABLE LENGTH	Up to 4ft (up to 1M)
---------------------	----------------------

CABLE TYPE	Passive
-------------------	---------

CONNECTOR GROUP	Micro USB USB-A
------------------------	--------------------



