



□□□□□

## Eaton ZPLA4-UNV1-EM-P

Eaton Crouse-Hinds series Pauluhn ZPLA linear LED light fixture, Cool white, 700 lm emergency mode, 4 ft, Glass lens, 7000 lm, 102 lm/W, Copper-free aluminum, Emergency battery back-up, 120-277 Vac, 127-300 Vdc, 73W

□□□□

|                             |                                                                 |
|-----------------------------|-----------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Pauluhn ZPLA linear LED light fixture |
| <b>CATALOG NUMBER</b>       | ZPLA4-UNV1-EM-P                                                 |
| <b>UPC</b>                  | 662276959088                                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 48.2 in                                                         |
| <b>PRODUCT HEIGHT</b>       | 4.56 in                                                         |
| <b>PRODUCT WIDTH</b>        | 6.5 in                                                          |
| <b>PRODUCT WEIGHT</b>       | 37.8 lb                                                         |

## Certifications and compliances

|                                        |                                                          |
|----------------------------------------|----------------------------------------------------------|
| <b>AREA CLASSIFICATION</b>             | Hazardous/Classified Locations                           |
| <b>STANDARDS TYPE</b>                  | NEC/CEC                                                  |
| <b>NEC HAZARDOUS RATING</b>            | Class I, Division 1<br>Class II, Division 1<br>Class III |
| <b>NEMA RATING</b>                     | 4X                                                       |
| <b>INGRESS PROTECTION (IP) RATINGS</b> | IP66                                                     |

## Product specifications

|                              |                           |
|------------------------------|---------------------------|
| <b>LAMP TYPE</b>             | LED                       |
| <b>COLOR TEMPERATURE</b>     | Cool white                |
| <b>LAMP LENGTH</b>           | 4 ft                      |
| <b>LUMENS</b>                | 7000                      |
| <b>EMERGENCY MODE LUMENS</b> | 700                       |
| <b>LUMENS PER WATT</b>       | 102                       |
| <b>VOLTAGE RATING</b>        | 120-277 Vac, 127-300 Vdc  |
| <b>FREQUENCY RATING</b>      | 50/60 Hz                  |
| <b>LENS MATERIAL</b>         | Glass                     |
| <b>MATERIAL</b>              | Copper-free aluminum      |
| <b>WATTAGE</b>               | 73 W                      |
| <b>POWER FACTOR</b>          | > 0.90                    |
| <b>SPECIAL FEATURES</b>      | Emergency battery back-up |

|         |                                                                                                                          |
|---------|--------------------------------------------------------------------------------------------------------------------------|
| 00000   | <a href="#">IF 1910 - Pauluhn Linear ZPLA LED Fixtures</a>                                                               |
|         | <a href="#">IF 1906 - Pauluhn Linear ZPLA LED Fixtures with EM</a>                                                       |
| 0000000 | <a href="#">Pauluhn ZPL LED Explosionproof Linear</a>                                                                    |
|         | <a href="#">Eaton Specification Sheet - ZPLA4-UNV1-EM-P</a>                                                              |
| 0000    | <a href="#">Crouse-Hinds series DLC approved lighting products</a>                                                       |
|         | <a href="#">Crouse-Hinds series Pauluhn ZPLA LED Linear brochure</a>                                                     |
| 0000    | <a href="#">Crouse-Hinds series Pauluhn ZPLA Linear LED catalog page</a>                                                 |
|         | <a href="#">Pauluhn ZPLA Explosionproof Linear LED Light Fixtures UL certification (ZPL4 with Battery Back-up)</a>       |
| 0000    | <a href="#">Pauluhn ZPLA Explosionproof Linear LED Light Fixtures Canadian certification (ZPL4 with Battery Back-up)</a> |
|         | <a href="#">Pauluhn ZPLA Explosionproof Linear LED Light Fixtures UL certification</a>                                   |
|         | <a href="#">Pauluhn ZPLA Explosionproof Linear LED Light Fixtures UL certification</a>                                   |
|         | <a href="#">Pauluhn ZPLA Explosionproof Linear LED Light Fixtures Canadian certification</a>                             |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

