



□□□□□

## Eaton 008141

Eaton Moeller® series T0 On-Off switch, T0, 20 A, service distribution board mounting, 3 contact unit(s), 3 pole + N, 1 N/O, 1 N/C, Emergency switching off function, with red thumb grip and yellow front plate

### □□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series T0 On-off switch
<b>CATALOG NUMBER</b>	008141
<b>PRODUCT LENGTH/DEPTH</b>	101 mm
<b>PRODUCT HEIGHT</b>	55 mm
<b>PRODUCT WIDTH</b>	54 mm
<b>PRODUCT WEIGHT</b>	0.144 kg
<b>CERTIFICATIONS</b>	CSA Class No.: 3211-05 UL File No.: E36332 UL IEC/EN 60204 VDE 0660 CSA-C22.2 No. 60947-4-1-14 CSA-C22.2 No. 94 UL 60947-4-1 CSA File No.: 012528 IEC/EN 60947-3 UL Category Control No.: NLRV CSA IEC/EN 60947 CE
<b>CATALOG NOTES</b>	Rated Short-time Withstand Current (Icw) for a time of 1 second



Powering Business Worldwide

□□□□	
PRODUCT CATEGORY	On-Off switch
FEATURES	Version as emergency stop installation
ACTUATOR COLOR	Red
ACTUATOR FUNCTION	Maintained
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-main-switch-declaration-of-conformity-uk251328en.pdf</a>
□□□□□	<a href="#">IL03801006Z</a>
□□□	<a href="#">eaton-rotary-switches-main-switch-t0-main-switch-wiring-diagram.eps</a>
□□	<a href="#">eaton-rotary-switches-mounting-t0-step-switch-dimensions-004.eps</a> <a href="#">eaton-general-rotary-switch-t0-step-switch-symbol-005.eps</a> <a href="#">eaton-rotary-switches-front-plate-t0-on-off-switch-symbol-003.eps</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Red thumb grip and yellow front plate
<b>OPERATING FREQUENCY</b>	1200 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 HZ</b>	7.5 kW
<b>RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 HZ</b>	5.5 kW
<b>RATED PERMANENT CURRENT AT AC-21, 400 V</b>	20 A
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	20 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>SWITCHING ANGLE</b>	90 °
<b>SWITCHING POWER AT</b>	5.5 kW

<b>400 V</b>	
<b>VOLTAGE PER CONTACT PAIR IN SERIES</b>	60 V
<b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>	5.5 kW
<b>DEVICE CONSTRUCTION</b>	Built-in device fixed built-in technique
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	0.32 kA 320 A, Contacts, 1 second
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>DESIGN</b>	15284
<b>MOUNTING POSITION</b>	As required
<b>ACTUATOR TYPE</b>	Short thumb-grip
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>	0.5 HP
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE</b>	1 HP
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE</b>	3 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>	1.5 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE</b>	3 HP
<b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>	7.5 HP
<b>ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE</b>	7.5 HP
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W

<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0.6 W
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	6 kA
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CONTROL CIRCUIT RELIABILITY</b>	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP30
<b>NUMBER OF POLES</b>	4
<b>MOUNTING METHOD</b>	Service distribution board mounting
<b>DEGREE OF PROTECTION</b>	NEMA Other
<b>SUITABLE FOR</b>	Ground mounting Branch circuits, suitable as motor disconnect, (UL/CSA) Distribution board installation
<b>FUNCTIONS</b>	Emergency switching off function
<b>NUMBER OF SWITCHES</b>	1
<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140
<b>SCREW SIZE</b>	M3.5, Terminal screw
<b>INSCRIPTION</b>	0-1
<b>SHOCK RESISTANCE</b>	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
<b>LIFESPAN, MECHANICAL</b>	400,000 Operations
<b>LOAD RATING</b>	2 x I <sub>e</sub> (with intermittent operation class 12, 25 % duty factor) 1.6 x I <sub>e</sub> (with intermittent operation class 12, 40 % duty factor) 1.3 x I <sub>e</sub> (with intermittent

	operation class 12, 60 % duty factor)
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)</b>	10A, IU, (UL/CSA)
<b>SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)</b>	A600 (UL/CSA) P300 (UL/CSA)
<b>TERMINAL CAPACITY</b>	18 - 14 AWG, solid or flexible with ferrule 1 x (0.75 - 2.5) mm <sup>2</sup> , flexible with ferrules to DIN 46228 1 x (1 - 2.5) mm <sup>2</sup> , solid or stranded 2 x (1 - 2.5) mm <sup>2</sup> , solid or stranded 2 x (0.75 - 2.5) mm <sup>2</sup> , flexible with ferrules to DIN 46228
<b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>	16 A, Rated uninterrupted current max. (UL/CSA)
<b>SAFETY PARAMETER (EN ISO 13849-1)</b>	B10d values as per EN ISO 13849-1, table C.1
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>NUMBER OF CONTACT UNITS</b>	3
<b>NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V</b>	1
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V</b>	3
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V</b>	1
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V</b>	5
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V</b>	2
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V</b>	3
<b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b>	100 A
<b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b>	110 A
<b>RATED BREAKING CAPACITY AT 500 V (COS</b>	80 A

<b>PHI TO IEC 60947-3)</b>	
<b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b>	60 A
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b>	130 A
<b>RATED OPERATING VOLTAGE (UE) - MAX</b>	690 V
<b>RATED OPERATING VOLTAGE (UE) - MIN</b>	690 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>SHORT-CIRCUIT CURRENT RATING (BASIC RATING)</b>	5 kA, SCCR (UL/CSA) 50A, max. Fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT CURRENT RATING (HIGH FAULT)</b>	10 kA, SCCR (UL/CSA) 20 A, Class J, max. Fuse, SCCR (UL/CSA)
<b>SHORT-CIRCUIT PROTECTION RATING</b>	20 A gG/gL, Fuse, Contacts
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>	20 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V</b>	13.3 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V</b>	13.3 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V</b>	13.3 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V</b>	7.6 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	11.5 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	11.5 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>	9 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	4.9 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1,</b>	10 A

<b>LOAD-BREAK SWITCHES</b> <b>L/R = 1 MS</b>	
<b>RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS</b>	10 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V</b>	1 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V</b>	5 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V</b>	10 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V</b>	5 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V</b>	10 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V</b>	10 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 220/230 V</b>	20 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 380/400 V</b>	20 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 500 V</b>	15.6 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 690 V</b>	8.5 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	20 A
<b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>	3 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>	5.5 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>	7.5 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>	5.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400</b>	5.5 kW

V, 50 HZ	
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	4 kW
RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 380/400 V, 50 HZ	7.5 kW
TIGHTENING TORQUE	8.8 lb-in, Screw terminals 1 Nm, Screw terminals
UNINTERRUPTED CURRENT	Rated uninterrupted current Iu is specified for max. cross-section.
HOUSING MATERIAL	Plastic
