

Eaton 008960

Eaton Moeller® series T3 Main switch, T3, 32 A, flush mounting, 4 contact unit(s), 7-pole, Emergency switching off function, With red rotary handle and yellow locking ring

PRODUCT NAME	Eaton Moeller® series T3 Main switch
CATALOG NUMBER	008960
PRODUCT LENGTH/DEPTH	139 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	65 mm
PRODUCT WEIGHT	0.282 kg
CERTIFICATIONS	UL File No.: E36332 CE CSA-C22.2 No. 60947-4-1-14 CSA File No.: 012528 IEC/EN 60947-3 VDE 0660 UL Category Control No.: NLRV IEC/EN 60947 UL CSA CSA-C22.2 No. 94 IEC/EN 60204 CSA Class No.: 3211-05 UL 60947-4-1
CATALOG NOTES	Rated Short-time Withstand Current (Icw) for a time of 1 second

PRODUCT CATEGORY	
	Main switch
FEATURES	
	Version as main switch Version as emergency stop installation Version as maintenance-/service switch
ACTUATOR COLOR	
	Red
10.10 TEMPERATURE RISE	
	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	
	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	
	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	
	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	
	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	
	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	
	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	
	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	
	UV resistance only in connection with protective shield.
10.2.5 LIFTING	
	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL	
	Does not apply, since the

IL03801020Z	
	eaton-rotary-switches-t0-on-off-switch-wiring-diagram-039.eps
	eaton-rotary-switches-t0-on-off-switch-wiring-diagram-040.eps
	eaton-rotary-switches-mounting-t3-main-switch-dimensions-004.eps

IMPACT	entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Red rotary handle and yellow locking ring
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 HZ	18.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 HZ	22 kW
RATED PERMANENT CURRENT AT AC-21, 400 V	32 A
RATED UNINTERRUPTED CURRENT (IU)	32 A

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	90 °
SWITCHING POWER AT 400 V	15 kW
VOLTAGE PER CONTACT PAIR IN SERIES	60 V
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	15 kW
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0.65 kA 650 A, Contacts, 1 second
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
DESIGN	8343
MOUNTING POSITION	As required
ACTUATOR TYPE	Door coupling rotary drive
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	1.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	3 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	3 HP

ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	10 HP
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	1.1 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	7
MOUNTING METHOD	Flush mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Branch circuits, suitable as motor disconnect, (UL/CSA) Front mounting center
FUNCTIONS	Emergency switching off function Interlockable
NUMBER OF SWITCHES	1
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
SCREW SIZE	M4, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-

	sinusoidal shock 20 ms
LIFESPAN, MECHANICAL	500,000 Operations
LOAD RATING	1.3 x I _e (with intermittent operation class 12, 60 % duty factor) 1.6 x I _e (with intermittent operation class 12, 40 % duty factor) 2 x I _e (with intermittent operation class 12, 25 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600 (UL/CSA) P600 (UL/CSA)
TERMINAL CAPACITY	1 x (0.75 - 4) mm ² , flexible with ferrules to DIN 46228 2 x (0.75 - 4) mm ² , flexible with ferrules to DIN 46228 14 - 10 AWG, solid or flexible with ferrule 2 x (1 - 6) mm ² , solid or stranded 1 x (1 - 6) mm ² , solid or stranded
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	25 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACT UNITS	4
NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V	5
NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2

NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	3
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	260 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	260 A
RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	240 A
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	170 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	320 A
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	40A, max. Fuse, SCCR (UL/CSA) 5 kA, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT)	10 kA, SCCR (UL/CSA) 40 A, Class J, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING	35 A gG/gL, Fuse, Contacts
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	32 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	32 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	32 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	26.4 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	17 A
RATED OPERATIONAL CURRENT (IE) AT AC-3,	23.7 A

220 V, 230 V, 240 V	
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	23.7 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	23.7 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	14.7 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS	20 A
RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V	1 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	12 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	25 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 220/230 V	32 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 380/400 V	32 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 500 V	32 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 690 V	25.5 A
RATED OPERATIONAL CURRENT FOR SPECIFIED	32 A

HEAT DISSIPATION (IN)	
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	11 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	11 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	11 kW
RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 380/400 V, 50 HZ	15 kW
TIGHTENING TORQUE	1.6 Nm, Screw terminals 17.7 lb-in, Screw terminals
UNINTERRUPTED CURRENT	Rated uninterrupted current I _u is specified for max. cross-section.

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: