



00000

Eaton 010091

Eaton Moeller® series DILER Contactor relay, 220 V DC, N/O = Normally open: 2 N/O, N/C = Normally closed: 2 NC, Screw terminals, DC operation

0000

PRODUCT NAME	Eaton Moeller® series DILER Control relay
CATALOG NUMBER	010091
PRODUCT LENGTH/DEPTH	54 mm
PRODUCT HEIGHT	58 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.206 kg
CERTIFICATIONS	CSA Class No.: 3211-03 UL 508 CSA IEC/EN 60947 EN 60947-5-1 UL IEC/EN 60947-4-1 UL File No.: E29184 CE CSA-C22.2 No. 14-05 CSA File No.: 012528 VDE 0660 UL Category Control No.: NKCR

0000

FEATURES

Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF PROTECTION OF

Does not apply, since the entire switchgear needs to

00

DECLARATIONS OF CONFORMITY

[eaton-control-relay-declaration-of-conformity-uk251243en.pdf](#)

SYSTEM OVERVIEW

[eaton-contactors-diler-relay-explosion-drawing.eps](#)

00000

[IL03407009Z](#)

000

[eaton-contactors-contact-diler-relay-wiring-diagram-006.eps](#)

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Interlocked opposing contacts
OPERATING FREQUENCY	9000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.4 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0

NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS, DELAYED SWITCHING)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS, LEADING)	0
POWER CONSUMPTION (PICK-UP) AT DC	2.3 W
POWER CONSUMPTION (SEALING) AT DC	2.3 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
SWITCHING TIME (DC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN	26 ms
SWITCHING TIME (DC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX	25 ms
SWITCHING TIME (DC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN	15 ms
SWITCHING TIME (DC OPERATED, N/O, WITH AUXILIARY CONTACT MODULE, CLOSING DELAY)	70 ms
APPLICATION	Contactor relays
PRODUCT CATEGORY	DILER Mini-contactors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
CONVENTIONAL	
THERMAL CURRENT ITH AT 50°C (3-POLE, OPEN)	10 A
VOLTAGE TYPE OF OPERATING VOLTAGE	AC/DC
RATED SWITCH CURRENT	10 A
OPERATING VOLTAGE AT AC, 50 HZ - MIN	17 V

OPERATING VOLTAGE AT AC, 50 HZ - MAX	500 V
OPERATING VOLTAGE AT AC, 60 HZ - MIN	17 V
OPERATING VOLTAGE AT AC, 60 HZ - MAX	500 V
OPERATING VOLTAGE AT DC - MIN	24 VDC
OPERATING VOLTAGE AT DC - MAX	220 VDC
SCREWDRIVER SIZE	2, Terminal screw, Pozidriv screwdriver 0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver
VOLTAGE TYPE	DC
CODE NUMBER	22E
DEGREE OF PROTECTION	IP20
MOUNTING POSITION	As required (except vertical with terminals A1/A2 at the bottom)
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	< 2 λ , < 1 failure at 100,000,000 Operations (at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)
CONNECTION TYPE (AUXILIARY CIRCUIT)	Screw connection
DUTY FACTOR	100 %
LIFESPAN, MECHANICAL	20,000,000 Operations (DC operated)
MOUNTING METHOD	DIN-rail/screw
PICK-UP VOLTAGE	0.85 - 1.3 V DC x U_c 0.7 - 1.3 V DC x U_c (at 24 V: without auxiliary contact module and at ambient air temperature + 40 °C)
VOLTAGE TOLERANCE	Smoothed DC, three-phase bridge rectifiers or smoothed double-wave rectification
SAFE ISOLATION	300 V AC, Between coil and auxiliary contacts, According to EN 61140 300 V AC, Between auxiliary contacts, According to EN 61140
SCREW SIZE	M3.5, Terminal screw
RATED OPERATIONAL CURRENT (IE)	2.5 A at 60 V, DC L/R ≤ 15 ms (with 2 contacts in

series)	
0.5 A at 220 V, DC L/R \leq 15	
ms (with 3 contacts in	
series)	
2.5 A at 24 V, DC L/R \leq 15	
ms (with 1 contact in	
series)	
1.5 A at 110 V, DC L/R \leq 15	
ms (with 3 contacts in	
series)	
10 A	
SWITCHING CAPACITY	
(AUXILIARY CONTACTS,	0.5 A, 250 V DC, (UL/CSA)
GENERAL USE)	10 A, 600 V AC, (UL/CSA)
SWITCHING CAPACITY	
(AUXILIARY CONTACTS,	A600, AC operated
PILOT DUTY)	(UL/CSA)
P300, DC operated	
(UL/CSA)	
RATED CONTROL SUPPLY	
VOLTAGE (US) AT DC -	220 V
MAX	
RATED CONTROL SUPPLY	
VOLTAGE (US) AT DC -	220 V
MIN	
RATED INSULATION	
VOLTAGE (UI)	690 V
RATED OPERATIONAL	
CURRENT (IE) AT AC-15,	6 A
220 V, 230 V, 240 V	
RATED OPERATIONAL	
CURRENT (IE) AT AC-15,	3 A
380 V, 400 V, 415 V	
RATED OPERATIONAL	
CURRENT (IE) AT AC-15,	1.5 A
500 V	
RATED OPERATIONAL	
CURRENT FOR SPECIFIED	6 A
HEAT DISSIPATION (IN)	
RATED OPERATIONAL	
VOLTAGE (UE) AT AC -	600 V
MAX	
STATIC HEAT	
DISSIPATION, NON-	
CURRENT-DEPENDENT	2.3 W
PVS	
STRIPPING LENGTH	
(MAIN CABLE)	8 mm
SWITCHING TIME (DC	
OPERATED, MAKE	
CONTACTS, CLOSING	35 ms
DELAY) - MAX	
TERMINAL CAPACITY	
(FLEXIBLE WITH	2 x (0.75 - 1.5) mm ²
FERRULE)	1 x (0.75 - 1.5) mm ²

SHOCK RESISTANCE	8 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms 10 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half- sinusoidal shock 10 ms
SHORT-CIRCUIT PROTECTION RATING	10 A fast, 500V, Maximum fuse, Short-circuit rating without welding, Contacts
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14 2 x (18 - 14) 1 x (18 - 14)
SHORT-CIRCUIT PROTECTION RATING WITHOUT WELDING	6 A gG/gL, 500 V, Max. Fuse, Contacts
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 2.5) mm ² 2 x (0.75 - 2.5) mm ²
TIGHTENING TORQUE	1.2 Nm, Screw terminals
ACTUATING VOLTAGE	220 V DC

□□□□:

□□□□:

□□□:

□□: