



□□□□□

## Eaton 011585

Eaton Moeller® series T0 Voltmeter selector switch, 20 A, center mounting, 2 contact units, Contacts: 4, 45 °, maintained, 0 (Off) position, 0-Phase/N, Design no. 8005

□□□□

|                             |                                                                                                                                                                                                                                                           |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Moeller® series T0 Voltmeter selector switch                                                                                                                                                                                                        |
| <b>CATALOG NUMBER</b>       | 011585                                                                                                                                                                                                                                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 106 mm                                                                                                                                                                                                                                                    |
| <b>PRODUCT HEIGHT</b>       | 48 mm                                                                                                                                                                                                                                                     |
| <b>PRODUCT WIDTH</b>        | 48 mm                                                                                                                                                                                                                                                     |
| <b>PRODUCT WEIGHT</b>       | 0.124 kg                                                                                                                                                                                                                                                  |
| <b>CERTIFICATIONS</b>       | UL Category Control No.: NLRV<br>IEC/EN 60947-3<br>UL File No.: E36332<br>CSA-C22.2 No. 60947-4-1-14<br>VDE 0660<br>IEC/EN 60204<br>CSA File No.: 012528<br>UL 60947-4-1<br>CSA<br>CE<br>IEC/EN 60947<br>CSA-C22.2 No. 94<br>CSA Class No.: 3211-05<br>UL |
| <b>CATALOG NOTES</b>        | Rated Short-time Withstand Current (Icw) for a time of 1 second                                                                                                                                                                                           |

| 0000                                                                             |                                                                                                                                  |
|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| TYPE                                                                             | Voltmeter selector switch                                                                                                        |
| PRODUCT CATEGORY                                                                 | Control switches                                                                                                                 |
| ACTUATOR FUNCTION                                                                | With 0 (Off) position Maintained                                                                                                 |
| 10.10 TEMPERATURE RISE                                                           | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING                                                       | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 ELECTROMAGNETIC COMPATIBILITY                                              | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 MECHANICAL FUNCTION                                                        | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| 10.2.2 CORROSION RESISTANCE                                                      | Meets the product standard's requirements.                                                                                       |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES                         | Meets the product standard's requirements.                                                                                       |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT       | Meets the product standard's requirements.                                                                                       |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements.                                                                                       |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION                                 | UV resistance only in connection with protective shield.                                                                         |
| 10.2.5 LIFTING                                                                   | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.6 MECHANICAL IMPACT                                                         | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.7 INSCRIPTIONS                                                              | Meets the product standard's requirements.                                                                                       |
| 10.3 DEGREE OF PROTECTION OF                                                     | Does not apply, since the entire switchgear needs to                                                                             |

| 00                         |                                                                                                                                                                                            |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DECLARATIONS OF CONFORMITY | <a href="#">eaton-step-switch-declaration-of-conformity-uk251327en.pdf</a>                                                                                                                 |
| 00000                      | <a href="#">IL03801020Z</a>                                                                                                                                                                |
| 000                        | <a href="#">eaton-rotary-switches-t0-voltmeter-selector-switch-wiring-diagram-015.eps</a><br><br><a href="#">eaton-rotary-switches-t0-voltmeter-selector-switch-wiring-diagram-016.eps</a> |
| 00                         | <a href="#">eaton-rotary-switches-mounting-t0-step-switch-dimensions-010.eps</a><br><br><a href="#">eaton-rotary-switches-front-plate-t0-voltmeter-selector-switch-symbol-004.eps</a>      |

|                                                                 |                                                                                |
|-----------------------------------------------------------------|--------------------------------------------------------------------------------|
| <b>ASSEMBLIES</b>                                               | be evaluated.                                                                  |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                                     |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                                         |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                                         |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                                         |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                                         |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                                         |
| <b>FITTED WITH:</b>                                             | 0 (off) position<br>Black thumb grip and front plate<br>Control unit           |
| <b>OPERATING FREQUENCY</b>                                      | 1200 Operations/h                                                              |
| <b>POLLUTION DEGREE</b>                                         | 3                                                                              |
| <b>CLIMATIC PROOFING</b>                                        | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| <b>ENCLOSURE MATERIAL</b>                                       | Plastic                                                                        |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 6000 V AC                                                                      |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 50 °C                                                                          |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C                                                                         |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>           | 40 °C                                                                          |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>           | -25 °C                                                                         |
| <b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>        | 0.5 HP                                                                         |
| <b>ASSIGNED MOTOR POWER AT 200/208 V, 60</b>                    | 1 HP                                                                           |

|                                                                    |                                                                                                  |
|--------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|
| <b>HZ, 1-PHASE</b>                                                 |                                                                                                  |
| <b>ASSIGNED MOTOR<br/>POWER AT 200/208 V, 60<br/>HZ, 3-PHASE</b>   | 3 HP                                                                                             |
| <b>ASSIGNED MOTOR<br/>POWER AT 230/240 V, 60<br/>HZ, 1-PHASE</b>   | 1.5 HP                                                                                           |
| <b>ASSIGNED MOTOR<br/>POWER AT 230/240 V, 60<br/>HZ, 3-PHASE</b>   | 3 HP                                                                                             |
| <b>ASSIGNED MOTOR<br/>POWER AT 460/480 V, 60<br/>HZ, 3-PHASE</b>   | 7.5 HP                                                                                           |
| <b>ASSIGNED MOTOR<br/>POWER AT 575/600 V, 60<br/>HZ, 3-PHASE</b>   | 7.5 HP                                                                                           |
| <b>EQUIPMENT HEAT<br/>DISSIPATION, CURRENT-<br/>DEPENDENT PVID</b> | 0 W                                                                                              |
| <b>HEAT DISSIPATION<br/>CAPACITY PDISS</b>                         | 0 W                                                                                              |
| <b>HEAT DISSIPATION PER<br/>POLE, CURRENT-<br/>DEPENDENT PVID</b>  | 0.6 W                                                                                            |
| <b>NUMBER OF CONTACT<br/>UNITS</b>                                 | 2                                                                                                |
| <b>DEVICE CONSTRUCTION</b>                                         | Front installation                                                                               |
| <b>RATED SHORT-TIME<br/>WITHSTAND CURRENT<br/>(ICW)</b>            | 320 A, Contacts, 1 second                                                                        |
| <b>MOUNTING POSITION</b>                                           | As required                                                                                      |
| <b>RATED CONDITIONAL<br/>SHORT-CIRCUIT CURRENT<br/>(IQ)</b>        | 6 kA                                                                                             |
| <b>MOUNTING METHOD</b>                                             | Center mounting                                                                                  |
| <b>OVERVOLTAGE<br/>CATEGORY</b>                                    | III                                                                                              |
| <b>CONTROL CIRCUIT<br/>RELIABILITY</b>                             | 1 failure per 100,000<br>switching operations<br>statistically determined, at<br>24 V DC, 10 mA) |
| <b>NUMBER OF POLES</b>                                             | 2                                                                                                |
| <b>DEGREE OF PROTECTION</b>                                        | NEMA 12<br>IP65                                                                                  |
| <b>NUMBER OF CONTACTS</b>                                          | 4                                                                                                |
| <b>DEGREE OF PROTECTION<br/>(FRONT SIDE)</b>                       | IP65                                                                                             |
| <b>INSCRIPTION</b>                                                 | " 0-Phase/N "                                                                                    |
| <b>SWITCH FUNCTION TYPE</b>                                        | 3 x phase-N                                                                                      |
| <b>FUNCTIONS</b>                                                   | Measuring between phase                                                                          |

|                                                                      |                                                                                                                                                                                                                                               |
|----------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                      | and N-neutral possible                                                                                                                                                                                                                        |
| <b>LIFESPAN, MECHANICAL</b>                                          | 400,000 Operations                                                                                                                                                                                                                            |
| <b>SAFE ISOLATION</b>                                                | 440 V AC, Between the contacts, According to EN 61140                                                                                                                                                                                         |
| <b>RATED OPERATIONAL CURRENT (IE)</b>                                | 8.5 A at AC-3, 690 V star-delta<br>20 A at AC-3, 400 V star-delta<br>20 A at AC-3, 230 V star-delta<br>15.6 A at AC-3, 500 V star-delta                                                                                                       |
| <b>SCREW SIZE</b>                                                    | M3.5, Terminal screw                                                                                                                                                                                                                          |
| <b>SHOCK RESISTANCE</b>                                              | 15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms                                                                                                                                                                 |
| <b>LOAD RATING</b>                                                   | 1.6 x I <sub>e</sub> (with intermittent operation class 12, 40 % duty factor)<br>2 x I <sub>e</sub> (with intermittent operation class 12, 25 % duty factor)<br>1.3 x I <sub>e</sub> (with intermittent operation class 12, 60 % duty factor) |
| <b>SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)</b>          | 10A, IU, (UL/CSA)                                                                                                                                                                                                                             |
| <b>TIGHTENING TORQUE</b>                                             | 8.8 lb-in, Screw terminals<br>1 Nm, Screw terminals                                                                                                                                                                                           |
| <b>SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)</b>           | P300 (UL/CSA)<br>A600 (UL/CSA)                                                                                                                                                                                                                |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V</b>                 | 1                                                                                                                                                                                                                                             |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V</b>                 | 3                                                                                                                                                                                                                                             |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V</b>                  | 1                                                                                                                                                                                                                                             |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V</b>                 | 5                                                                                                                                                                                                                                             |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V</b>                  | 2                                                                                                                                                                                                                                             |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V</b>                  | 3                                                                                                                                                                                                                                             |
| <b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b> | 100 A                                                                                                                                                                                                                                         |

|                                                                      |                                                                                                                      |
|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| <b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b> | 110 A                                                                                                                |
| <b>RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)</b>     | 80 A                                                                                                                 |
| <b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b> | 60 A                                                                                                                 |
| <b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b> | 130 A                                                                                                                |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>                | 20 A                                                                                                                 |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V</b>               | 13.3 A                                                                                                               |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V</b>        | 13.3 A                                                                                                               |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V</b>               | 13.3 A                                                                                                               |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V</b>               | 7.6 A                                                                                                                |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>   | 11.5 A                                                                                                               |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>   | 11.5 A                                                                                                               |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>                 | 9 A                                                                                                                  |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>          | 4.9 A                                                                                                                |
| <b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>               | 16 A, Rated uninterrupted current max. (UL/CSA)                                                                      |
| <b>SAFETY PARAMETER (EN ISO 13849-1)</b>                             | B10d values as per EN ISO 13849-1, table C.1                                                                         |
| <b>SHORT-CIRCUIT PROTECTION RATING</b>                               | 20 A gG/gL, Fuse, Contacts                                                                                           |
| <b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>                     | 1 x (0.75 - 2.5) mm <sup>2</sup> , ferrules to DIN 46228<br>2 x (0.75 - 2.5) mm <sup>2</sup> , ferrules to DIN 46228 |
| <b>SUITABLE FOR</b>                                                  | Branch circuits, suitable as motor disconnect,                                                                       |

|                                                                               | (UL/CSA) |
|-------------------------------------------------------------------------------|----------|
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS</b> | 10 A     |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS</b>  | 10 A     |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V</b>                         | 1 A      |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V</b>                        | 5 A      |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V</b>                         | 10 A     |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V</b>                        | 5 A      |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V</b>                         | 10 A     |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V</b>                         | 10 A     |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>          | 20 A     |
| <b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>                    | 3 kW     |
| <b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>                        | 5.5 kW   |
| <b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>                        | 7.5 kW   |
| <b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>                        | 5.5 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>                          | 5.5 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>                          | 4 kW     |
| <b>RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ</b>                 | 5.5 kW   |
| <b>RATED OPERATIONAL POWER STAR-DELTA AT</b>                                  | 7.5 kW   |

|                                                     |                                                                     |
|-----------------------------------------------------|---------------------------------------------------------------------|
| 380/400 V, 50 HZ                                    |                                                                     |
| RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 HZ  | 7.5 kW                                                              |
| RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 HZ  | 5.5 kW                                                              |
| RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX          | 690 V                                                               |
| RATED UNINTERRUPTED CURRENT (IU)                    | 20 A                                                                |
| STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS  | 0 W                                                                 |
| SWITCHING ANGLE                                     | 45 °                                                                |
| VOLTAGE PER CONTACT PAIR IN SERIES                  | 60 V                                                                |
| SHORT-CIRCUIT CURRENT RATING (HIGH FAULT)           | 20 A, Class J, max. Fuse, SCCR (UL/CSA)<br>10 kA, SCCR (UL/CSA)     |
| SHORT-CIRCUIT CURRENT RATING (BASIC RATING)         | 50A, max. Fuse, SCCR (UL/CSA)<br>5 kA, SCCR (UL/CSA)                |
| TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE AWG) | 18 - 14                                                             |
| TERMINAL CAPACITY (SOLID/STRANDED)                  | 2 x (1 - 2.5) mm <sup>2</sup><br>1 x (1 - 2.5) mm <sup>2</sup>      |
| UNINTERRUPTED CURRENT                               | Rated uninterrupted current Iu is specified for max. cross-section. |
| DESIGN                                              | 8005                                                                |

|       |
|-------|
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |