



00000

Eaton 012254

Eaton Moeller® series T0 Reversing switch,
20 A, flush mounting, 3 contact units,
Contacts: 5, 90 °, maintained, 1-2, Design
number 115

0000

PRODUCT NAME	Eaton Moeller® series T0 Reversing switch
CATALOG NUMBER	012254
PRODUCT LENGTH/DEPTH	95 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	0.132 kg
CERTIFICATIONS	CSA File No.: 012528 UL File No.: E36332 VDE 0660 CSA CSA-C22.2 No. 60947-4-1- 14 CSA Class No.: 3211-05 IEC/EN 60947 UL CSA-C22.2 No. 94 IEC/EN 60947-3 UL 60947-4-1 UL Category Control No.: NLRV CE IEC/EN 60204
CATALOG NOTES	Rated Short-time Withstand Current (Icw) for a time of 1 second

0000

TYPE	Reversing switch
PRODUCT CATEGORY	Control switches
ACTUATOR FUNCTION	Maintained Without 0 (Off) position
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

00

DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
00000	IL03801020Z
000	eaton-rotary-switches-t0-reversing-switch-wiring-diagram-015.eps
000	eaton-rotary-switches-t0-reversing-switch-wiring-diagram-016.eps
	eaton-rotary-switches-mounting-t0-step-switch-dimensions-026.eps
00	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-014.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
ENCLOSURE MATERIAL	Plastic
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	0.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	1 HP

ASSIGNED MOTOR
POWER AT 200/208 V, 60 3 HP
Hz, 3-PHASE

ASSIGNED MOTOR
POWER AT 230/240 V, 60 1.5 HP
Hz, 1-PHASE

ASSIGNED MOTOR
POWER AT 230/240 V, 60 3 HP
Hz, 3-PHASE

ASSIGNED MOTOR
POWER AT 460/480 V, 60 7.5 HP
Hz, 3-PHASE

ASSIGNED MOTOR
POWER AT 575/600 V, 60 7.5 HP
Hz, 3-PHASE

EQUIPMENT HEAT
DISSIPATION, CURRENT- 0 W
DEPENDENT PVID

HEAT DISSIPATION 0 W
CAPACITY PDISS

HEAT DISSIPATION PER
POLE, CURRENT- 0.6 W
DEPENDENT PVID

NUMBER OF AUXILIARY
CONTACTS (CHANGE- 0
OVER CONTACTS)

NUMBER OF AUXILIARY
CONTACTS (NORMALLY 0
CLOSED CONTACTS)

NUMBER OF AUXILIARY
CONTACTS (NORMALLY 0
OPEN CONTACTS)

NUMBER OF CONTACT 3
UNITS

RATED SHORT-TIME
WITHSTAND CURRENT 320 A, Contacts, 1 second
(ICW)

ELECTRICAL
CONNECTION TYPE OF Screw connection
MAIN CIRCUIT

MOUNTING POSITION As required

RATED CONDITIONAL
SHORT-CIRCUIT CURRENT 6 kA
(IQ)

MOUNTING METHOD Flush mounting

OVERVOLTAGE III
CATEGORY

CONTROL CIRCUIT 1 failure per 100,000
RELIABILITY switching operations
statistically determined, at
24 V DC, 10 mA)

NUMBER OF POLES 3

DEGREE OF PROTECTION	NEMA 1 IP65 NEMA 12
NUMBER OF CONTACTS	5
MODEL	Reversing switch
DEGREE OF PROTECTION (FRONT SIDE)	IP65 NEMA 12
INSCRIPTION	1-2
LIFESPAN, MECHANICAL	400,000 Operations
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
RATED OPERATIONAL CURRENT (IE)	20 A at AC-3, 400 V star-delta 15.6 A at AC-3, 500 V star-delta 8.5 A at AC-3, 690 V star-delta 20 A at AC-3, 230 V star-delta
SCREW SIZE	M3.5, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LOAD RATING	2 x I_e (with intermittent operation class 12, 25 % duty factor) 1.3 x I_e (with intermittent operation class 12, 60 % duty factor) 1.6 x I_e (with intermittent operation class 12, 40 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
TIGHTENING TORQUE	8.8 lb-in, Screw terminals 1 Nm, Screw terminals
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	P300 (UL/CSA) A600 (UL/CSA)
NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V	5

NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2
NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	3
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	100 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	110 A
RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	80 A
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	60 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	130 A
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	20 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	7.6 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	11.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	11.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	9 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	4.9 A
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	16 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1

SHORT-CIRCUIT PROTECTION RATING	20 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 2.5) mm ² , ferrules to DIN 46228 2 x (0.75 - 2.5) mm ² , ferrules to DIN 46228
SUITABLE FOR	Branch circuits, suitable as motor disconnect, (UL/CSA) Front mounting
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V	1 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	10 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 Hz	3 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 Hz	5.5 kW
RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 Hz	7.5 kW
RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 Hz	5.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400	4 kW

V, 50 Hz**RATED OPERATIONAL**

POWER AT AC-3, 415 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER AT AC-3, 690 V, 50 Hz 4 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 220/230 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 380/400 V, 50 Hz 7.5 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 500 V, 50 Hz 7.5 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 690 V, 50 Hz 5.5 kW

RATED OPERATIONAL

VOLTAGE (UE) AT AC - MAX 690 V

RATED UNINTERRUPTED CURRENT (IU)

20 A

STATIC HEAT

DISSIPATION, NON-CURRENT-DEPENDENT PVS 0 W

SWITCHING ANGLE

90 °

VOLTAGE PER CONTACT PAIR IN SERIES

60 V

SHORT-CIRCUIT CURRENT RATING (HIGH FAULT)

20 A, Class J, max. Fuse, SCCR (UL/CSA)
10 kA, SCCR (UL/CSA)

SHORT-CIRCUIT CURRENT RATING (BASIC RATING)

50A, max. Fuse, SCCR (UL/CSA)
5 kA, SCCR (UL/CSA)

TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE AWG)

18 - 14

TERMINAL CAPACITY (SOLID/STRANDED)

2 x (1 - 2.5) mm²
1 x (1 - 2.5) mm²

UNINTERRUPTED CURRENT

Rated uninterrupted current I_u is specified for max. cross-section.

DESIGN

115

□□□□:

□□□□⋮

10

11

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026 00 0000000

