



Eaton 011822

Eaton Moeller® series T0 Reversing switch, 20 A, rear mounting, Basic switch, 2 contact units, Contacts: 4, 45 °, Design number 8400

□□□□

PRODUCT NAME	Eaton Moeller® series T0 Reversing switch
CATALOG NUMBER	011822
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	0.088 kg
CERTIFICATIONS	CE

10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
ECAD MODEL	DA-CE-ETN.T0-2-8400_XZ
□□□	eaton-rotary-switches-reversing-switch-t0-reversing-switch-wiring-diagram.eps
□□	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-009.eps

AGAINST ELECTRIC SHOCK	entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	0 (off) position
POLLUTION DEGREE	3
ENCLOSURE MATERIAL	Plastic
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACT UNITS	2
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
MOUNTING POSITION	As required
MOUNTING METHOD	Rear mounting
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Three-pole
DEGREE OF PROTECTION	IP00 NEMA Other
NUMBER OF CONTACTS	4
MODEL	Reversing switch
DEGREE OF PROTECTION (FRONT SIDE)	IP00 NEMA Other
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	20 A

RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	11.5 A
SUITABLE FOR	Intermediate mounting Ground mounting Front mounting
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	4 kW
RATED UNINTERRUPTED CURRENT (IU)	20 A
SWITCHING ANGLE	45 °
DESIGN	8400

□□□□:
□□□□:
□□□:
□□: