

Eaton 034138

Eaton xEffect Ci Enclosures Switch- & Controlgear Enclosure. Insulated enclosure, smooth sides, HxWxD=375x375x175mm

PRODUCT NAME	Eaton xEffect Ci Enclosures Switch- & Controlgear Enclosure
CATALOG NUMBER	034138
PRODUCT LENGTH/DEPTH	175 mm
PRODUCT HEIGHT	375 mm
PRODUCT WIDTH	375 mm
PRODUCT WEIGHT	3.364 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN 61439-2 EN 62208

SPECIAL FEATURES	Smooth side plates, without knockouts Sealable cover fasteners Include fixing straps for wall mounting
TYPE	Basic enclosure Individual enclosures xEnergy Safety Ci
FEATURES	UV resistance beneath protective shield Cover with overpressure release
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	Meets the product standard's requirements.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Lower part: 960 °C / cover: 850 °C
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Not relevant to indoor installations.
10.2.5 LIFTING	20 kg per enclosure with support frame and lifting aid met; assembled and secured as per the latest applicable instruction leaflet.
10.2.6 MECHANICAL IMPACT	IK10

MCAD MODEL	ci44x_150.stp ci44x_150.dwg
	eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-006.eps eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-017.eps eaton-enclosures-mounting-xenergy-safety-ci-lv-systems-dimensions-005.eps eaton-enclosures-xenergy-safety-ci-lv-systems-dimensions-006.eps eaton-enclosures-enclosure-xenergy-safety-ci-lv-systems-dimensions-015.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	IP65
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Protection class 2, therefore not applicable.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Is the panel builder's responsibility.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 1000 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	8 kV
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Meets the product standard's requirements.
SURFACE FINISHING	Resistant to corrosion
DEGREE OF PROTECTION	IK10 IP65 Other
ENCLOSURE MATERIAL	Plastic
SURFACE PROTECTION	Other
CHEMICAL RESISTANCE	Resistant against: acids < 10 %, mineral oil, alcohol, gasoline, greases, salt solutions Partly resistant to: Acids > 10 % Not resistant to: alkalis, benzene
CIRCUIT INTEGRITY	Other
BASE TYPE	Plain
UNIT TYPE	Stand-alone device
BUILT-IN DEPTH	150 mm
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	27 W

HEAT DISS. AMBIENT 35°C DELTA T: 20°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	24 W
HEAT DISS. AMBIENT 35°C DELTA T:20°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	26 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT INDIVID. ENCL. TOP (IEC 60890)	54 W
HEAT DISS. AMBIENT 35°C DELTA T: 35°C WALL MOUNT MIDDLE ENCL. TOP (IEC 60890)	48 W
HEAT DISS. AMBIENT 35°C DELTA T:35°C WALL MOUNT STARTING ENCL. TOP (IEC 60890)	51 W
COLOR	Gray Light gray (RAL 7035, base) Transparent, smoky gray (cover)
COVER/DOOR COLOR	Transparent
COVER/DOOR MODEL	Closed
COVER/DOOR TYPE	Optional None Transparent
NUMBER OF OPENINGS (FLANGE PLATES)	0
PLATE THICKNESS (CABINET)	9 mm
PLATE THICKNESS (COVER/DOOR)	6 mm
RAL-NUMBER	7035
WIDTH IN NUMBER OF MODULAR SPACINGS	15
AMBIENT OPERATING TEMPERATURE DETAILS	-40 °C - 80 °C
MATERIAL	Halogen free Non-reinforced polycarbonate (cover) Glass-fibre reinforced polycarbonate (base)
MOUNTING METHOD	Surface mounted (plaster)
NUMBER OF ROWS	0
TEMPERATURE	Temperature resistant: -40

RESISTANCE	°C - 120 °C (enclosure) Temperature resistant: 80 °C (gasket) Temperature resistant: 85 °C (enclosure bolt)
FLAMMABILITY CHARACTERISTICS (UL)	V1 (base) (UL94) V2 (cover) (UL94)
PROTECTION CLASS	II
NUMBER OF MODULES	1
SURFACE TREATMENT	Resistant to corrosion
INTERNAL DEPTH	150 mm
MOUNTING DEPTH WITH MOUNTING PLATE	150 mm
NOMINAL CURRENT	1600 A
NUMBER OF CONDUIT INLETS	0
SUITABLE FOR	Lightning protection Outdoor use
SALINE SPRAY RESISTANCE	IEC 60068-2-11
ENCLOSURE MATERIAL QUALITY	Other
TYPE OF COATING	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

