

Eaton 035260

Eaton Moeller® series STI Control transformer, 3 kVA, Rated input voltage $400 \pm 5\%$ V, Rated output voltage 230 V

PRODUCT NAME	Eaton Moeller® series STI Control transformer
CATALOG NUMBER	035260
PRODUCT LENGTH/DEPTH	170 mm
PRODUCT HEIGHT	255 mm
PRODUCT WIDTH	230 mm
PRODUCT WEIGHT	27.588 kg
CERTIFICATIONS	CSA-C22.2 No. 66 UL File No.: E167225 VDE 0570 Part 2-2 UL Category Control No.: XPTQ2, XPTQ8 IEC/EN 61558-2-2/2-4/2-6 UL5085-1 CE UL report applies to both US and Canada Certified by UL for use in Canada CSA-C22.2 No. 66.1-06 IEC/EN 60204-1, ÖVE-EN 13 VDE 0570 Part 2-6 (safety transformers) VDE 0113, VDE 0100 Part 410 IEC/EN 61558-2-2 UL 5085-2 UL Recognized VDE 0570 Part 2-4 (isolating transformer) UL 506 CSA-C22.2 No. 66.2-06
CATALOG NOTES	Electrical characteristics: all details for no-load loss, short-circuit loss (copper losses), short-circuit voltage and efficiency values relate to a temperature of 20 °C

TYPE	Single-phase control, isolating and safety transformer
FEATURES	Separate windings Reinforced insulation Fully Vacuum-impregnated
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL	Is the panel builder's

SYSTEM OVERVIEW	eaton-general-diagram-sti-control-transformer-explosion-drawing-002.eps
	eaton-general-transformer-sti-control-transformer-dimensions-023.eps

ELECTRICAL CIRCUITS AND CONNECTIONS	responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
APPARENT POWER	3000 VA
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NO-LOAD LOSSES	30 W
PRIMARY VOLTAGE 1 - MAX	400 V
PRIMARY VOLTAGE 1 - MIN	400 V
PRIMARY VOLTAGE 10 - MAX	0 V
PRIMARY VOLTAGE 10 - MIN	0 V
PRIMARY VOLTAGE 2 - MAX	0 V
PRIMARY VOLTAGE 2 - MIN	0 V
PRIMARY VOLTAGE 3 - MAX	0 V
PRIMARY VOLTAGE 3 - MIN	0 V
PRIMARY VOLTAGE 4 - MAX	0 V
PRIMARY VOLTAGE 4 - MIN	0 V
PRIMARY VOLTAGE 5 - MAX	0 V
PRIMARY VOLTAGE 5 - MIN	0 V
PRIMARY VOLTAGE 6 - MAX	0 V
BUILT AS	Safety transformer Isolating transformer
CONDUCTOR MATERIAL	Copper
DEGREE OF	IP00

PROTECTION	
CONNECTION LUG	Yes for > 115 A
CONNECTION TYPE	Terminations, < 115 A
DUTY FACTOR	100 %
INSULATION MATERIAL TYPE (IEC 85)	B
EFFICIENCY	97 %
RELATIVE SHORT-CIRCUIT VOLTAGE	2.1 %
SUITABLE FOR	Branch circuits, (UL/CSA)
INSULATION CLASS	B
PRIMARY TAPPING	± 5 %
PRIMARY VOLTAGE 6 - MIN	0 V
PRIMARY VOLTAGE 7 - MAX	0 V
PRIMARY VOLTAGE 7 - MIN	0 V
PRIMARY VOLTAGE 8 - MAX	0 V
PRIMARY VOLTAGE 8 - MIN	0 V
PRIMARY VOLTAGE 9 - MAX	0 V
PRIMARY VOLTAGE 9 - MIN	0 V
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED POWER	3 VA
SECONDARY VOLTAGE 1 - MAX	230 V
SECONDARY VOLTAGE 1 - MIN	230 V
SECONDARY VOLTAGE 10 - MAX	0 V
SECONDARY VOLTAGE 10 - MIN	0 V
SECONDARY VOLTAGE 2 - MAX	0 V
SECONDARY VOLTAGE 2 - MIN	0 V
SECONDARY VOLTAGE 3 - MAX	0 V
SECONDARY VOLTAGE 3 - MIN	0 V
SECONDARY VOLTAGE 4 - MAX	0 V
PRODUCT CATEGORY	Single-phase control transformers ST

SECONDARY VOLTAGE 4 - MIN	0 V
SECONDARY VOLTAGE 5 - MAX	0 V
SECONDARY VOLTAGE 5 - MIN	0 V
SECONDARY VOLTAGE 6 - MAX	0 V
SECONDARY VOLTAGE 6 - MIN	0 V
SECONDARY VOLTAGE 7 - MAX	0 V
SECONDARY VOLTAGE 7 - MIN	0 V
SECONDARY VOLTAGE 8 - MAX	0 V
SECONDARY VOLTAGE 8 - MIN	0 V
SECONDARY VOLTAGE 9 - MAX	0 V
SECONDARY VOLTAGE 9 - MIN	0 V
SHORT-CIRCUIT LOSSES	55 W
SHORT-TIME RATING	11.5 kVA
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	85 W
VOLTAGE RATING - MAX	600 V
POWER CONSUMPTION IN STANDBY MODE	28 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: