



Eaton 043594

Eaton Moeller® series T0 Changeover switch, 20 A, service distr. board mounting, 4 contact units, Contacts: 8, 90 °, maintained, 0 (Off) position, 1-0-2, Design no. 8294

0000

PRODUCT NAME	Eaton Moeller® series T0 Changeover switch
CATALOG NUMBER	043594
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	55 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	0.179 kg
CERTIFICATIONS	CSA-C22.2 No. 60947-4-1-14 IEC/EN 60947 UL 60947-4-1 CSA File No.: 012528 IEC/EN 60204 CSA-C22.2 No. 94 CSA UL Category Control No.: NLRV CE IEC/EN 60947-3 UL File No.: E36332 CSA Class No.: 3211-05 UL VDE 0660
CATALOG NOTES	Rated Short-time Withstand Current (Icw) for a time of 1 second

0000

TYPE	Changeover switch
PRODUCT CATEGORY	Control switches
ACTUATOR FUNCTION	With 0 (Off) position Maintained
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

00

DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
00000	IL03801006Z
000	eaton-rotary-switches-changeover-switch-t0-changeover-switch-wiring-diagram-005.eps
	eaton-rotary-switches-mounting-t0-step-switch-dimensions-005.eps
	eaton-rotary-switches-mounting-t0-step-switch-dimensions.eps
00	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-011.eps
	eaton-rotary-switches-mounting-t0-changeover-switch-3d-drawing.eps
	eaton-general-rotary-switch-t0-step-switch-symbol-005.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	0 (off) position Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
ENCLOSURE MATERIAL	Plastic
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	0.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60	1 HP

HZ, 1-PHASE**ASSIGNED MOTOR****POWER AT 200/208 V, 60** 3 HP**HZ, 3-PHASE****ASSIGNED MOTOR****POWER AT 230/240 V, 60** 1.5 HP**HZ, 1-PHASE****ASSIGNED MOTOR****POWER AT 230/240 V, 60** 3 HP**HZ, 3-PHASE****ASSIGNED MOTOR****POWER AT 460/480 V, 60** 7.5 HP**HZ, 3-PHASE****ASSIGNED MOTOR****POWER AT 575/600 V, 60** 7.5 HP**HZ, 3-PHASE****EQUIPMENT HEAT****DISSIPATION, CURRENT-DEPENDENT PVID****HEAT DISSIPATION**

0 W

CAPACITY PDISS**HEAT DISSIPATION PER****POLE, CURRENT-DEPENDENT PVID****DEPENDENT PVID****NUMBER OF AUXILIARY****CONTACTS (CHANGE-OVER CONTACTS)** 0**NUMBER OF AUXILIARY****CONTACTS (NORMALLY CLOSED CONTACTS)** 0**NUMBER OF AUXILIARY****CONTACTS (NORMALLY OPEN CONTACTS)** 0**NUMBER OF CONTACT**

4

UNITS**RATED SHORT-TIME****WITHSTAND CURRENT (ICW)** 320 A, Contacts, 1 second**ELECTRICAL****CONNECTION TYPE OF MAIN CIRCUIT** Screw connection**MOUNTING POSITION**

As required

RATED CONDITIONAL**SHORT-CIRCUIT CURRENT (IQ)** 6 kA**MOUNTING METHOD**

Service distribution board mounting

OVERVOLTAGE

III

CATEGORY**CONTROL CIRCUIT**

1 failure per 100,000

RELIABILITY

switching operations

statistically determined, at

	24 V DC, 10 mA)
NUMBER OF POLES	4
DEGREE OF PROTECTION	IP30
NUMBER OF CONTACTS	8
MODEL	Reverser
DEGREE OF PROTECTION (FRONT SIDE)	IP30 NEMA 2
INSCRIPTION	1-0-2
LIFESPAN, MECHANICAL	400,000 Operations
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
RATED OPERATIONAL CURRENT (IE)	8.5 A at AC-3, 690 V star-delta 20 A at AC-3, 230 V star-delta 20 A at AC-3, 400 V star-delta 15.6 A at AC-3, 500 V star-delta
SCREW SIZE	M3.5, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LOAD RATING	1.3 x I_e (with intermittent operation class 12, 60 % duty factor) 2 x I_e (with intermittent operation class 12, 25 % duty factor) 1.6 x I_e (with intermittent operation class 12, 40 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
TIGHTENING TORQUE	8.8 lb-in, Screw terminals 1 Nm, Screw terminals
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	P300 (UL/CSA) A600 (UL/CSA)
NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V	5

V

NUMBER OF CONTACTS
IN SERIES AT DC-23A, 48 V

2

NUMBER OF CONTACTS
IN SERIES AT DC-23A, 60 V

3

RATED BREAKING

CAPACITY AT 220/230 V 100 A
(COS PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 400/415 V 110 A
(COS PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 500 V (COS 80 A
PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 660/690 V 60 A
(COS PHI TO IEC 60947-3)

RATED MAKING

CAPACITY UP TO 690 V 130 A
(COS PHI TO IEC/EN
60947-3)

RATED OPERATIONAL

CURRENT (IE) AT AC-21, 20 A
440 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A
230 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A
400 V, 415 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A
500 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 7.6 A
690 V

RATED OPERATIONAL

CURRENT (IE) AT AC-3, 11.5 A
220 V, 230 V, 240 V

RATED OPERATIONAL

CURRENT (IE) AT AC-3, 11.5 A
380 V, 400 V, 415 V

RATED OPERATIONAL

CURRENT (IE) AT AC-3, 9 A
500 V

RATED OPERATIONAL

CURRENT (IE) AT AC-3, 4.9 A
660 V, 690 V

SWITCHING CAPACITY
(MAIN CONTACTS,
GENERAL USE)

16 A, Rated uninterrupted
current max. (UL/CSA)

SAFETY PARAMETER (EN

B10d values as per EN ISO

ISO 13849-1)	13849-1, table C.1
SHORT-CIRCUIT PROTECTION RATING	20 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	2 x (0.75 - 2.5) mm ² , ferrules to DIN 46228 1 x (0.75 - 2.5) mm ² , ferrules to DIN 46228
SUITABLE FOR	Branch circuits, suitable as motor disconnect, (UL/CSA) Ground mounting Distribution board installation Front mounting
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V	1 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	10 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ	3 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ	7.5 kW
RATED OPERATIONAL	5.5 kW

**POWER AT AC-23A, 690 V,
50 Hz**

RATED OPERATIONAL

**POWER AT AC-3, 380/400
V, 50 Hz**

RATED OPERATIONAL

**POWER AT AC-3, 415 V, 50
Hz**

RATED OPERATIONAL

**POWER AT AC-3, 690 V, 50
Hz**

RATED OPERATIONAL

**POWER STAR-DELTA AT
220/230 V, 50 Hz**

RATED OPERATIONAL

**POWER STAR-DELTA AT
380/400 V, 50 Hz**

RATED OPERATIONAL

**POWER STAR-DELTA AT
500 V, 50 Hz**

RATED OPERATIONAL

**POWER STAR-DELTA AT
690 V, 50 Hz**

RATED OPERATIONAL

**VOLTAGE (UE) AT AC -
MAX**

**RATED UNINTERRUPTED
CURRENT (IU)**

20 A

STATIC HEAT

**DISSIPATION, NON-
CURRENT-DEPENDENT**

0 W

PVS

SWITCHING ANGLE

90 °

**VOLTAGE PER CONTACT
PAIR IN SERIES**

60 V

**SHORT-CIRCUIT CURRENT
RATING (HIGH FAULT)**

20 A, Class J, max. Fuse,
SCCR (UL/CSA)
10 kA, SCCR (UL/CSA)

**SHORT-CIRCUIT CURRENT
RATING (BASIC RATING)**

50A, max. Fuse, SCCR
(UL/CSA)
5 kA, SCCR (UL/CSA)

**TERMINAL CAPACITY
(SOLID/FLEXIBLE WITH
FERRULE AWG)**

18 - 14

**TERMINAL CAPACITY
(SOLID/STRANDED)**

1 x (1 - 2.5) mm²
2 x (1 - 2.5) mm²

**UNINTERRUPTED
CURRENT**

Rated uninterrupted
current lu is specified for
max. cross-section.

DESIGN

8294

□□□□:

四

10

11

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026

