



□□□□□

## Eaton 044977

Eaton Moeller® series P1 Panic switches, P1, 32 A, flush mounting, 3 pole, with black thumb grip and front plate, Cylinder lock SVA

□□□□

|                                 |                                                            |
|---------------------------------|------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Moeller® series P1<br>Panic switch                   |
| <b>CATALOG NUMBER</b>           | 044977                                                     |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 139 mm                                                     |
| <b>PRODUCT HEIGHT</b>           | 73 mm                                                      |
| <b>PRODUCT WIDTH</b>            | 49 mm                                                      |
| <b>PRODUCT WEIGHT</b>           | 0.267 kg                                                   |
| <b>CERTIFICATIONS</b>           | IEC/EN 60947<br>IEC/EN 60947-3<br>VDE 0660<br>IEC/EN 60204 |

| □□□□                                                                             |                                                                                                                                  |
|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| TYPE                                                                             | Panic switch                                                                                                                     |
| PRODUCT CATEGORY                                                                 | Switch with locking mechanism                                                                                                    |
| ACTUATOR COLOR                                                                   | Black                                                                                                                            |
| ACTUATOR FUNCTION                                                                | Maintained                                                                                                                       |
| 10.10 TEMPERATURE RISE                                                           | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING                                                       | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 ELECTROMAGNETIC COMPATIBILITY                                              | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 MECHANICAL FUNCTION                                                        | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| 10.2.2 CORROSION RESISTANCE                                                      | Meets the product standard's requirements.                                                                                       |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES                         | Meets the product standard's requirements.                                                                                       |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT       | Meets the product standard's requirements.                                                                                       |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements.                                                                                       |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION                                 | UV resistance only in connection with protective shield.                                                                         |
| 10.2.5 LIFTING                                                                   | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.6 MECHANICAL IMPACT                                                         | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| 10.2.7 INSCRIPTIONS                                                              | Meets the product standard's requirements.                                                                                       |

| □□                         |                                                                                       |
|----------------------------|---------------------------------------------------------------------------------------|
| DECLARATIONS OF CONFORMITY | <a href="#">eaton-on-off-switch-declaration-of-conformity-uk251288en.pdf</a>          |
| □□□□□                      | <a href="#">IL03801015Z</a>                                                           |
| □□□                        | <a href="#">eaton-rotary-switches-on-off-switch-p3-main-switch-wiring-diagram.eps</a> |
| □□                         | <a href="#">eaton-rotary-switches-front-plate-t0-on-off-switch-symbol-002.eps</a>     |

|                                                                 |                                                                                |
|-----------------------------------------------------------------|--------------------------------------------------------------------------------|
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                                     |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                                         |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                                         |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                                         |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                                         |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                                         |
| <b>FITTED WITH:</b>                                             | Black thumb grip and front plate                                               |
| <b>OPERATING FREQUENCY</b>                                      | 1200 Operations/h                                                              |
| <b>POLLUTION DEGREE</b>                                         | 3                                                                              |
| <b>CLIMATIC PROOFING</b>                                        | Damp heat, cyclic, to IEC 60068-2-30<br>Damp heat, constant, to IEC 60068-2-78 |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 6000 V AC                                                                      |
| <b>RATED PERMANENT CURRENT AT AC-21, 400 V</b>                  | 32 A                                                                           |
| <b>RATED PERMANENT CURRENT AT AC-23, 400 V</b>                  | 32 A                                                                           |
| <b>RATED UNINTERRUPTED CURRENT (IU)</b>                         | 32 A                                                                           |
| <b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>       | 0 W                                                                            |
| <b>SWITCHING ANGLE</b>                                          | 90 °                                                                           |
| <b>SWITCHING POWER AT 400 V</b>                                 | 15 kW                                                                          |
| <b>VOLTAGE PER CONTACT PAIR IN SERIES</b>                       | 60 V                                                                           |

|                                                                |                                                                                                                                                                |
|----------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>ACCESSORIES</b>                                             | <ul style="list-style-type: none"> <li>• 2 keys included with supplied equipment.</li> <li>• Auxiliary contact or neutral conductor fitted by user.</li> </ul> |
| <b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>           | 18.5 kW                                                                                                                                                        |
| <b>DEVICE CONSTRUCTION</b>                                     | Built-in device fixed built-in technique                                                                                                                       |
| <b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>                | 0.64 kA<br>640 A, Contacts, 1 second                                                                                                                           |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>              | Screw connection                                                                                                                                               |
| <b>MOUNTING POSITION</b>                                       | As required                                                                                                                                                    |
| <b>ACTUATOR TYPE</b>                                           | Short thumb-grip                                                                                                                                               |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                     | 50 °C                                                                                                                                                          |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                     | -25 °C                                                                                                                                                         |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>          | 40 °C                                                                                                                                                          |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>          | -25 °C                                                                                                                                                         |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>      | 0 W                                                                                                                                                            |
| <b>HEAT DISSIPATION CAPACITY PDISS</b>                         | 0 W                                                                                                                                                            |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>       | 1.8 W                                                                                                                                                          |
| <b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>     | 0                                                                                                                                                              |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b> | 0                                                                                                                                                              |
| <b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>            | 80 kA                                                                                                                                                          |
| <b>OVERVOLTAGE CATEGORY</b>                                    | III                                                                                                                                                            |
| <b>CONTROL CIRCUIT RELIABILITY</b>                             | 1 failure per 100,000 switching operations statistically determined, at                                                                                        |

|                                                              |                                                                                                                                                                                                                                                  |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                              | 24 V DC, 10 mA)                                                                                                                                                                                                                                  |
| <b>DEGREE OF PROTECTION (FRONT SIDE)</b>                     | IP65                                                                                                                                                                                                                                             |
| <b>NUMBER OF POLES</b>                                       | 3                                                                                                                                                                                                                                                |
| <b>MOUNTING METHOD</b>                                       | Flush mounting                                                                                                                                                                                                                                   |
| <b>DEGREE OF PROTECTION</b>                                  | NEMA 12                                                                                                                                                                                                                                          |
| <b>SUITABLE FOR</b>                                          | Front mounting 4-hole                                                                                                                                                                                                                            |
| <b>LOCKING FACILITY</b>                                      | Lockable in the 0 (Off) position                                                                                                                                                                                                                 |
| <b>NUMBER OF SWITCHES</b>                                    | 1                                                                                                                                                                                                                                                |
| <b>SAFE ISOLATION</b>                                        | 440 V AC, Between the contacts, According to EN 61140                                                                                                                                                                                            |
| <b>SCREW SIZE</b>                                            | M4, Terminal screw                                                                                                                                                                                                                               |
| <b>INSCRIPTION</b>                                           | 0-1                                                                                                                                                                                                                                              |
| <b>SHOCK RESISTANCE</b>                                      | 15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms                                                                                                                                                                    |
| <b>LIFESPAN, MECHANICAL</b>                                  | 300,000 Operations                                                                                                                                                                                                                               |
| <b>LOCKING MECHANISM</b>                                     | Cylinder lock SVA                                                                                                                                                                                                                                |
| <b>LOAD RATING</b>                                           | $2 \times I_e$ (with intermittent operation class 12, 25 % duty factor)<br>$1.3 \times I_e$ (with intermittent operation class 12, 60 % duty factor)<br>$1.6 \times I_e$ (with intermittent operation class 12, 40 % duty factor)                |
| <b>TERMINAL CAPACITY</b>                                     | 1 x (1.5 - 6) mm <sup>2</sup> , solid or stranded<br>1 x (1 - 4) mm <sup>2</sup> , flexible with ferrules to DIN 46228<br>2 x (1.5 - 6) mm <sup>2</sup> , solid or stranded<br>2 x (1 - 4) mm <sup>2</sup> , flexible with ferrules to DIN 46228 |
| <b>SAFETY PARAMETER (EN ISO 13849-1)</b>                     | B10d values as per EN ISO 13849-1, table C.1                                                                                                                                                                                                     |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b> | 0                                                                                                                                                                                                                                                |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V</b>         | 3                                                                                                                                                                                                                                                |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V</b>          | 1                                                                                                                                                                                                                                                |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V</b>          | 2                                                                                                                                                                                                                                                |
| <b>NUMBER OF CONTACTS</b>                                    | 2                                                                                                                                                                                                                                                |

|                                                                      |                            |
|----------------------------------------------------------------------|----------------------------|
| <b>IN SERIES AT DC-23A, 60 V</b>                                     |                            |
| <b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b> | 260 A                      |
| <b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b> | 300 A                      |
| <b>RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)</b>     | 290 A                      |
| <b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b> | 250 A                      |
| <b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b> | 320 A                      |
| <b>RATED OPERATING VOLTAGE (UE) - MAX</b>                            | 690 V                      |
| <b>RATED OPERATING VOLTAGE (UE) - MIN</b>                            | 690 V                      |
| <b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>                    | 690 V                      |
| <b>SHORT-CIRCUIT PROTECTION RATING</b>                               | 50 A gG/gL, Fuse, Contacts |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>                | 32 A                       |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V</b>               | 32 A                       |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V</b>        | 32 A                       |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V</b>               | 30 A                       |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V</b>               | 19.8 A                     |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>   | 26.4 A                     |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>   | 26.4 A                     |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>                 | 23.4 A                     |
| <b>RATED OPERATIONAL CURRENT (IE) AT AC-3,</b>                       | 14.7 A                     |

|                                                                               |                                                                                 |
|-------------------------------------------------------------------------------|---------------------------------------------------------------------------------|
| <b>660 V, 690 V</b>                                                           |                                                                                 |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS</b> | 32 A                                                                            |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V</b>                        | 12 A                                                                            |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V</b>                         | 25 A                                                                            |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V</b>                         | 25 A                                                                            |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V</b>                         | 25 A                                                                            |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>          | 32 A                                                                            |
| <b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>                    | 7.5 kW                                                                          |
| <b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>                        | 15 kW                                                                           |
| <b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>                        | 18.5 kW                                                                         |
| <b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>                        | 15 kW                                                                           |
| <b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>                      | 13 kW                                                                           |
| <b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>                          | 13 kW                                                                           |
| <b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>                          | 15 kW                                                                           |
| <b>TIGHTENING TORQUE</b>                                                      | 14.1 lb-in, Screw terminals<br>1.6 Nm, Screw terminals                          |
| <b>UNINTERRUPTED CURRENT</b>                                                  | Rated uninterrupted current I <sub>u</sub> is specified for max. cross-section. |
| <b>HOUSING COLOR</b>                                                          | Black                                                                           |
| <b>HOUSING MATERIAL</b>                                                       | Plastic                                                                         |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

