



Eaton 070131

Eaton Moeller® series TM ON-OFF switches, TM, 10 A, flush mounting, 1 contact unit(s), Contacts: 1, 90 °, maintained, With 0 (Off) position, 0-1, Design number 8290

□□□□

PRODUCT NAME	Eaton Moeller® series TM On-off switch
CATALOG NUMBER	070131
PRODUCT LENGTH/DEPTH	62 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.029 kg
CERTIFICATIONS	CE UL report applies to both US and Canada Certified by UL for use in Canada UL UL 508 CSA UL Category Control No.: NLRV CSA-C22.2 No. 94 UL File No.: E36332 VDE 0660 IEC/EN 60947-5-1 CSA-C22.2 No. 14-05 IEC/EN 60947 IEC/EN 60947-3

□□□□	
TYPE	ON-OFF switch
PRODUCT CATEGORY	Control switches
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	With 0 (Off) position Maintained
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□	
DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251335en.pdf
□□□□□	IL03801025Z
□□□	eaton-rotary-switches-on-off-switch-t0-on-off-switch-wiring-diagram.eps
□□	eaton-rotary-switches-mounting-tm-step-switch-dimensions-005.eps eaton-rotary-switches-mounting-tm-step-switch-dimensions.eps eaton-rotary-switches-emergency-tm-on-off-switch-symbol.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
RATED PERMANENT CURRENT AT AC-21, 400 V	0 A
RATED UNINTERRUPTED CURRENT (IU)	10 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	90 °
SWITCHING POWER AT 400 V	0 kW
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA

ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
DESIGN	8290
MOUNTING POSITION	As required
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	0.33 HP
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 3-PHASE	0.75 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	0.75 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	1 HP
ASSIGNED MOTOR POWER AT 277 V, 60 HZ, 1-PHASE	0.75 HP
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0.15 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	0 kA
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	1

MOUNTING METHOD	Flush mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Front mounting 4-hole
NUMBER OF SWITCHES	1
SCREW SIZE	M2.5, Terminal screw
INSCRIPTION	0-1
LIFESPAN, MECHANICAL	1,000,000 Operations
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A300 (UL/CSA)
TERMINAL CAPACITY	14 AWG, solid or flexible with ferrule 2 x 1.0 mm ² , flexible with ferrules to DIN 46228 2 x 1,5 mm ² , solid or stranded 1 x 1.5 mm ² , flexible 1 x 1.0 mm ² , flexible with ferrules to DIN 46228 2 x 1.5 mm ² , flexible 1 x 1.5 mm ² , solid or stranded
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	10 A, Rated uninterrupted current max. (UL/CSA)
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACT UNITS	1
RATED OPERATING VOLTAGE (UE) - MAX	500 V
RATED OPERATING VOLTAGE (UE) - MIN	500 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	500 V
SHORT-CIRCUIT PROTECTION RATING	10 A gG/gL, Fuse, Contacts
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	10 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	10 A
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	3 kW

RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	0 kW
TIGHTENING TORQUE	0.4 Nm, Screw terminals 3.5 lb-in, Screw terminals
UNINTERRUPTED CURRENT	Rated uninterrupted current Iu is specified for max. cross-section.
HOUSING COLOR	Black
HOUSING MATERIAL	Plastic

□□□□:
□□□□:
□□□:
□□: