



Eaton 072378

Eaton Moeller® series RMQ16 Key-operated actuator, 3 positions, black, maintained Q25S3R

□□□□

PRODUCT NAME	Eaton Moeller® series RMQ16 Key-operated actuator
CATALOG NUMBER	072378
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	25 mm
PRODUCT WIDTH	25 mm
PRODUCT WEIGHT	0.023 kg
CERTIFICATIONS	CSA UL Category Control No.: NKCR CSA File No.: 46552 IEC/EN 60947 IEC/EN 60947-5 UL File No.: E29184 CSA-C22.2 No. 14-05 CSA Class No.: 3211-03 UL UL 508 CE



Powering Business Worldwide

□□□□

TYPE	Key-operated button
ACCESSORIES	1 key included with supplied equipment.
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Maintained Switching function latching Key withdrawable in position 0 Key withdrawable in position 2
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

DECLARATIONS OF CONFORMITY	eaton-accessory-declaration-of-conformity-uk251027en.pdf
□□□□□	IL04716016Z
□□	eaton-operating-rmq16-key-operated-actuator-dimensions.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	1800 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
ACTUATOR TYPE	Key
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-	0 W

DEPENDENT PVID	
OPENING DIAMETER	16 mm
OPENING HEIGHT	0 mm
OPERATING TORQUE	0.4 Nm
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	24 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	45 °
WIDTH OPENING	0 mm
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Black
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
BEZEL MATERIAL	Plastic
TERMINAL CAPACITY	0.5 - 1.0 mm ²
DESIGN	Key operated
MOUNTING POSITION	As required
TERMINAL SIZE	2.8 x 0.8 mm to DIN 46244, Blade terminal 2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA) 1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA)
DEGREE OF PROTECTION	NEMA 1
DEGREE OF PROTECTION (FRONT SIDE)	IP65
INDICATOR COLOR	Other

LENS TYPE	Square
LIFESPAN, MECHANICAL	3,000,000 Operations
NUMBER OF SWITCH POSITIONS	3
SIZE	Front dimensions: 25 × 25 mm
PRODUCT CATEGORY	RMQ16

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

