



Eaton 065362

Eaton xEnergy Safety Ci LV systems LV switchgear. N rail with terminal for fuse enclosure tab RS27/I43, 2x 2.5-35 and 18x 0.5-6mm²

□□□□

PRODUCT NAME	Eaton xEnergy Safety Ci N + PE/N rail
CATALOG NUMBER	065362
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	400 mm
PRODUCT WEIGHT	0.258 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH

RS27/I43 (I44)
SE-RS-I43 (I44)
Prepared enclosures
Modular busbar system
Ci insulated enclosure

TYPE

- Ci insulated enclosure
- Modular busbar system
- Prepared enclosures

FEATURES

Contact safe

ACCESSORY/SPARE PART TYPE

N bars

UNIT TYPE

Modular system

CONNECTION TYPE

Clamp
Screwing

NUMBER OF POLES

Single-pole

MOUNTING METHOD

Screw

SUITABLE FOR

Useful for stranded conductors

TERMINAL CAPACITY (SOLID WIRE)

0.5 mm² - 16 mm² (18x)
2.5 mm² - 35 mm² (2x)

NOMINAL CURRENT

63 A

NUMBER OF CONNECTIONS (LESS THAN 6 MM SQUARED)

0

NUMBER OF CONNECTIONS (LESS THAN AWG 6)

0

NUMBER OF CONNECTIONS (GREATER THAN 25 MM SQUARED)

2

NUMBER OF CONNECTIONS (GREATER THAN 250 KCMIL)

0

NUMBER OF CONNECTIONS (10 MM SQUARED)

0

NUMBER OF CONNECTIONS (16 MM SQUARED)

4

NUMBER OF CONNECTIONS (25 MM SQUARED)

0

NUMBER OF CONNECTIONS (250 KCMIL)

0

□□

□□□□□

[IL0713](#)

□□□□

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

□□□□

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

NUMBER OF CONNECTIONS (AWG 2)	0
NUMBER OF CONNECTIONS (AWG 4)	0
NUMBER OF CONNECTIONS (AWG 4/0)	0
NUMBER OF CONNECTIONS (AWG 6)	0
NUMBER OF CONNECTIONS (TOTAL)	6
NUMBER OF OUTPUTS	19
TERMINAL CAPACITY (STRANDED CABLE)	0.5 mm ² - 4 mm ² (18x) 2.5 mm ² - 25 mm ² (2x)
CONDUCTOR CROSS SECTION, INPUT - MAX	35 mm ²
CONDUCTOR CROSS SECTION, OUTPUT - MIN	0.5 mm ²
CONDUCTOR CROSS SECTION, INPUT - MIN	2.5 mm ²
CONDUCTOR CROSS SECTION, INPUT AWG - MIN	2 mm ²
CONDUCTOR CROSS SECTION, INPUT AWG - MAX	14 mm ²
CONDUCTOR CROSS SECTION, OUTPUT - MAX	6 mm ²
CONDUCTOR CROSS SECTION, OUTPUT AWG - MAX	20 mm ²
CONDUCTOR CROSS SECTION, OUTPUT AWG - MIN	10 mm ²
NUMBER OF INPUTS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

