

## Eaton 082152

Eaton Moeller® series L-PKZ0 Indicator light, white, 400V neon lamp

<b>PRODUCT NAME</b>	Eaton Moeller® series L-PKZ0 Accessory Indicator light
<b>CATALOG NUMBER</b>	082152
<b>PRODUCT LENGTH/DEPTH</b>	50 mm
<b>PRODUCT HEIGHT</b>	17 mm
<b>PRODUCT WIDTH</b>	17 mm
<b>PRODUCT WEIGHT</b>	0.01 kg
<b>COMPLIANCES</b>	CE

PRODUCT CATEGORY	
	Accessories
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Please enquire
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF</b>	Does not apply, since the entire switchgear needs to

MCAD MODEL	
	<a href="#">l_pkz0.stp</a> <a href="#">l_pkz0.dwg</a>
	<a href="#">IL03402035Z</a>
	<a href="#">eaton-manual-motor-starters-mounting-l-pkz0-indicator-light-dimensions.eps</a>
	<a href="#">eaton-manual-motor-starters-indication-l-pkz0-indicator-light-3d-drawing.eps</a>
	<a href="#">eaton-operating-button-symbol-013.eps</a>
	<a href="#">eaton-contactors-indication-l-pkz0-indicator-light-3d-drawing.eps</a>

<b>ASSEMBLIES</b>	be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>ELECTRIC CONNECTION TYPE</b>	Cable
<b>FITTED WITH:</b>	Light source
<b>BEZEL COLOR</b>	Other
<b>LAMP SOCKET TYPE</b>	Other
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	55 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>NUMBER OF PILOT LIGHTS</b>	10
<b>OPENING DIAMETER</b>	16 mm
<b>OPENING HEIGHT</b>	0 mm
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	0 A
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	400 V

BEZEL MATERIAL	Plastic
DEGREE OF PROTECTION	IP65 NEMA Other
LENS COLOR	White
VOLTAGE TYPE	AC/DC
RATED OPERATIONAL VOLTAGE (UE) - MIN	230 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	400 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	230 V
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0.46 W
WIDTH OPENING	0 mm
COLOR	White
LENS TYPE	Flat Rectangular
RATED CONTROL SUPPLY VOLTAGE	230 - 400 V (Us)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

