



Eaton 087793

Eaton Moeller® series MCS Pressure switch,
2W gold-plated, 15bar

□□□□

PRODUCT NAME	Eaton Moeller® series MCS Pressure switch
---------------------	--

CATALOG NUMBER	087793
-----------------------	--------

PRODUCT LENGTH/DEPTH	111 mm
-----------------------------	--------

PRODUCT HEIGHT	66 mm
-----------------------	-------

PRODUCT WIDTH	96 mm
----------------------	-------

PRODUCT WEIGHT	0.383 kg
-----------------------	----------

CERTIFICATIONS	CSA IEC/EN 60947-5-1 CSA File No.: 012528 CSA-CC22.2 No. 14 CSA Class No.: 3211-06
-----------------------	--

CATALOG NOTES

- Note on use: This product complies with Low-Voltage Directive 2014/35/EC and EMC Directive 2014/30/EC and meets the requirements in EN 60947-5-1. This product does not meet the rail industry's standard requirements. Accordingly, the user must review it separately for the specific application at hand.
- If required: pressure pipe flange R ½"



Powering Business Worldwide

□□□□

SUITABLE AS	2-point controller Guard
FEATURES	Variable switching differential
THREAD SIZE	1/2 inch 1/4 inch
ELECTRIC CONNECTION TYPE	Screw connection
OPERATING FREQUENCY	1500 Operations/h
POLLUTION DEGREE	3
ACTUATOR DIAMETER	0 mm
ADJUSTABLE CURRENT RANGE - MAX	0 A
ADJUSTABLE CURRENT RANGE - MIN	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BURSTING PRESSURE	90 bar
END SETTING - MAX	0 hPa
END SETTING - MIN	0 hPa
END VALUE MEASURING RANGE PRESSURE	0 Pa
ENGAGING PRESSURE - MAX	10.4 bar
ENGAGING PRESSURE - MIN	0 bar
INITIAL SETTING - MAX	0 hPa
INITIAL SETTING - MIN	0 hPa
INITIAL VALUE MEASURING RANGE PRESSURE	0 Pa
MEDIUM TEMPERATURE - MAX	80 °C
MEDIUM TEMPERATURE - MIN	25 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	2
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
CLIMATIC PROOFING	Damp heat, constant, to

□□

CHARACTERISTIC CURVE	eaton-pressure-switches- diagram-mcs-pressure- switch-characteristic- curve-002.eps
DECLARATIONS OF CONFORMITY	eaton-pressure-switch- declaration-of-conformity- uk251028en.pdf
MCAD MODEL	mcs_n.dwg mcs_n.stp
□□□□□	IL05212001Z
□□	eaton-pressure-switches- mcs-pressure-switch- dimensions.eps eaton-pressure-switches- switch-mcs-pressure- switch-dimensions- 003.eps eaton-pressure-switches- switch-mcs-pressure- switch-dimensions.eps

	IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
DEGREE OF PROTECTION	IP65 NEMA Other
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	1500 V AC
ENVIRONMENTAL CONDITIONS	Compliant to 2014/35/EC, 2014/30/EC and EN 60947-5-1. Accordingly, the user must review it separately for the specific application at hand.
CONNECTION	Inner thread gas cylindrical (BSPP)
MOUNTING POSITION	Vertical and 90° in all directions
CONNECTION TYPE	Tunnel terminal
OVERVOLTAGE CATEGORY	III
LIFESPAN, ELECTRICAL	1,000,000 Operations
NUMBER OF CONTACTS (NORMALLY CLOSED) AS MAIN CONTACT	0
NUMBER OF MAIN CONTACTS (NORMALLY OPEN CONTACT)	0
OPERATING PRESSURE - MAX	15000 hPa
PRESSURE DIFFERENTIAL	0 bar
RATED FREQUENCY - MAX	50 Hz
RATED INSULATION VOLTAGE (UI)	125 V
RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	0 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	0 A
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	0 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	0 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	0 V
RATED OPERATIONAL	110 V

VOLTAGE (UE) AT DC - MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
SWITCH OFF PRESSURE - MAX	11 bar
SWITCH OFF PRESSURE - MIN	0 bar
SWITCHING CAPACITY AT AC-3, 240 V	0 kA
TEST PRESSURE	32 bar
PRODUCT CATEGORY	Pressure switches
SCREW SIZE	M2.6, Terminal screw
RATED OPERATIONAL CURRENT (IE)	1 A at DC-13, 24 V 2 A at AC-15, 230 V, 50/60Hz 0.25 A at DC-13, 110 V
SHOCK RESISTANCE	10 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
SHORT-CIRCUIT PROTECTION RATING	Max. 2 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 2.5) mm ² 2 x (0.75 - 1.5) mm ²
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.5 - 1.5) mm ² , ferrules to DIN 46228
TIGHTENING TORQUE	0.4 Nm, Screw terminals
VIBRATION RESISTANCE	36 Hz, Amplitude 1 mm, (IEC/EN 60068-2-6)

□□□□:
□□□□:
□□□:
□□: