

Eaton 088585

Eaton Moeller® series RMQ16 Indicator light, raised, yellow Q18LH-GE

PRODUCT NAME	Eaton Moeller® series RMQ16 Indicator light
CATALOG NUMBER	088585
PRODUCT LENGTH/DEPTH	59 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	0.009 kg
CERTIFICATIONS	CSA CSA-C22.2 No. 14-05 UL CE IEC/EN 60947 IEC/EN 60947-5 UL 508 CSA Class No.: 3211-03 CSA File No.: 46552 UL Category Control No.: NKCR UL File No.: E29184

TYPE	Indicator lights
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC	Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY	DA-DC-00004136.pdf
	DA-DC-00004158.pdf
	IL04716016Z
	eaton-operating-indication-rmq16-indicator-light-dimensions.eps
	eaton-operating-button-rmq16-symbol-003.eps
	eaton-operating-indication-rmq16-indicator-light-3d-drawing.eps

SHOCK	be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring LED W2x4, 6d, max. 30 V, 1 W
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
BEZEL COLOR	Black
SHOCK RESISTANCE	40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Plastic
TERMINAL CAPACITY	0.5 - 1.0 mm ²
LENS COLOR	Yellow
DESIGN	Conical
MOUNTING POSITION	As required
TERMINAL SIZE	2.8 x 0.8 mm to DIN 46244, Blade terminal 2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors
OVERVOLTAGE	III

CATEGORY	
DEGREE OF PROTECTION	NEMA 1
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	16 mm
OPENING HEIGHT	16 mm
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	24 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SUITABLE FOR NUMBER OF BUILT-IN SIGNAL LIGHTS	1
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ16
SIZE	Front dimensions: 18 x 18 mm
DEGREE OF PROTECTION (FRONT SIDE)	IP65
LENS TYPE	Square High

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

