



□□□□

## Eaton 096062

Eaton Moeller® series T5 Insulated enclosure, Star-delta switch, 100 A, flush mounting, 4 contact units, Contacts: 8, 60 °, maintained, 0 (Off) position, 0-Y-D, Design number 3

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series T5 Insulated enclosure
<b>CATALOG NUMBER</b>	096062
<b>PRODUCT LENGTH/DEPTH</b>	141 mm
<b>PRODUCT HEIGHT</b>	88 mm
<b>PRODUCT WIDTH</b>	88 mm
<b>PRODUCT WEIGHT</b>	0.725 kg
<b>CERTIFICATIONS</b>	IEC/EN 60947 IEC/EN 60947-3 VDE 0660 IEC/EN 60204
<b>CATALOG NOTES</b>	Rated Short-time Withstand Current (I <sub>cw</sub> ) for a time of 1 second



Powering Business Worldwide

□□□□

<b>TYPE</b>	Star-delta switch
<b>PRODUCT CATEGORY</b>	Control switches
<b>ACTUATOR FUNCTION</b>	Maintained With 0 (Off) position
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	UV resistance only in connection with protective shield.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF</b>	Does not apply, since the entire switchgear needs to

□□

□□□□□	<a href="#">IL03801009Z</a>
□□□	<a href="#">eaton-rotary-switches-t0-star-delta-switch-wiring-diagram-004.eps</a>
	<a href="#">eaton-rotary-switches-t0-star-delta-switch-wiring-diagram-003.eps</a>
□□	<a href="#">eaton-rotary-switches-mounting-t5b-non-standard-switch-dimensions-004.eps</a>
	<a href="#">eaton-rotary-switches-front-plate-t0-star-delta-switch-symbol-006.eps</a>

<b>ASSEMBLIES</b>	be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Black thumb grip and front plate 0 (off) position
<b>OPERATING FREQUENCY</b>	1200 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>ENCLOSURE MATERIAL</b>	Plastic
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>ACTUATOR TYPE</b>	Short thumb-grip
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W

<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	7.5 W
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>NUMBER OF CONTACT UNITS</b>	4
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	1,7 kA, Contacts, 1 second
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>MOUNTING POSITION</b>	As required
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	2 kA
<b>MOUNTING METHOD</b>	Flush mounting
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CONTROL CIRCUIT RELIABILITY</b>	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
<b>NUMBER OF POLES</b>	3
<b>DEGREE OF PROTECTION</b>	NEMA 12 IP65
<b>NUMBER OF CONTACTS</b>	8
<b>MODEL</b>	Star-delta switch
<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP65 NEMA 12
<b>INSCRIPTION</b>	0-Y-D
<b>LIFESPAN, MECHANICAL</b>	500,000 Operations
<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140
<b>RATED OPERATIONAL CURRENT (IE)</b>	76.2 A at AC-3, 500 V star-delta 100 A at AC-3, 230 V star-delta 29.4 A at AC-3, 690 V star-delta 95.3 A at AC-3, 400 V star-delta

<b>SCREW SIZE</b>	M6, Terminal screw
<b>SHOCK RESISTANCE</b>	15 g, Mechanical, According to IEC/EN 60068-2-27, Half- sinusoidal shock 20 ms
<b>LOAD RATING</b>	2 x I <sub>e</sub> (with intermittent operation class 12, 25 % duty factor) 1.3 x I <sub>e</sub> (with intermittent operation class 12, 60 % duty factor) 1.6 x I <sub>e</sub> (with intermittent operation class 12, 40 % duty factor)
<b>TIGHTENING TORQUE</b>	4 Nm, Screw terminals
<b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b>	760 A
<b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b>	740 A
<b>RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)</b>	590 A
<b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b>	420 A
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b>	950 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>	100 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V</b>	100 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V</b>	100 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V</b>	55 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V</b>	32 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	71 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	55 A
<b>RATED OPERATIONAL</b>	44 A

<b>CURRENT (IE) AT AC-3, 500 V</b>	
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	17 A
<b>SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)</b>	65 A, Rated uninterrupted current max. (UL/CSA)
<b>SAFETY PARAMETER (EN ISO 13849-1)</b>	B10d values as per EN ISO 13849-1, table C.1
<b>SHORT-CIRCUIT PROTECTION RATING</b>	100 A gG/gL, Fuse, Contacts
<b>TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)</b>	1 x (1 - 25) mm <sup>2</sup> , ferrules to DIN 46228 2 x (1.5 - 10) mm <sup>2</sup> , ferrule to DIN 46228
<b>SUITABLE FOR</b>	Front mounting
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS</b>	80 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	100 A
<b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>	30 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>	55 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>	37 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>	30 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>	45 kW
<b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>	30 kW
<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	15 kW
<b>RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ</b>	30 kW
<b>RATED OPERATIONAL POWER STAR-DELTA AT 380/400 V, 50 HZ</b>	45 kW
<b>RATED OPERATIONAL</b>	45 kW

