



□□□□□

Eaton 098862

Eaton Moeller® series T0 Changeover switch, 20 A, flush mounting, 1 contact unit, Contacts: 2, 90 °, maintained, USV-NETZ, Design no. 15541

□□□□

PRODUCT NAME	Eaton Moeller® series T0 Changeover switch
CATALOG NUMBER	098862
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	8 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	0.083 kg
CERTIFICATIONS	CSA CSA-C22.2 No. 60947-4-1-14 IEC/EN 60204 CSA File No.: 012528 CSA-C22.2 No. 94 VDE 0660 IEC/EN 60947 CE UL Category Control No.: NLRV UL 60947-4-1 IEC/EN 60947-3 UL CSA Class No.: 3211-05 UL File No.: E36332
CATALOG NOTES	Rated Short-time Withstand Current (Icw) for a time of 1 second

□□□□	
TYPE	Changeover switch
PRODUCT CATEGORY	Control switches
ACTUATOR FUNCTION	Maintained Without 0 (Off) position
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

□□	
DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
□□□□□	IL03801020Z
□□□	eaton-rotary-switches-t0-changeover-switch-wiring-diagram-061.eps eaton-rotary-switches-t0-changeover-switch-wiring-diagram-062.eps
□□	eaton-rotary-switches-mounting-t0-step-switch-dimensions-034.eps eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-008.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
ENCLOSURE MATERIAL	Plastic
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	0.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	1 HP

ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	3 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	1.5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	3 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	7.5 HP
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0.6 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACT UNITS	1
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	320 A, Contacts, 1 second
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
MOUNTING POSITION	As required
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	6 kA
MOUNTING METHOD	Flush mounting
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
NUMBER OF POLES	1

DEGREE OF PROTECTION	NEMA 1 NEMA 12 IP65
NUMBER OF CONTACTS	2
MODEL	Reverser
DEGREE OF PROTECTION (FRONT SIDE)	IP65 NEMA 12
INSCRIPTION	" USV-NETZ "
LIFESPAN, MECHANICAL	400,000 Operations
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
RATED OPERATIONAL CURRENT (IE)	20 A at AC-3, 400 V star-delta 20 A at AC-3, 230 V star-delta 15.6 A at AC-3, 500 V star-delta 8.5 A at AC-3, 690 V star-delta
SCREW SIZE	M3.5, Terminal screw
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LOAD RATING	2 x I _e (with intermittent operation class 12, 25 % duty factor) 1.6 x I _e (with intermittent operation class 12, 40 % duty factor) 1.3 x I _e (with intermittent operation class 12, 60 % duty factor)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10A, IU, (UL/CSA)
TIGHTENING TORQUE	1 Nm, Screw terminals 8.8 lb-in, Screw terminals
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600 (UL/CSA) P300 (UL/CSA)
NUMBER OF CONTACTS IN SERIES AT DC-21A, 240 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V	5

NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2
NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	3
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	100 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	110 A
RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	80 A
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	60 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	130 A
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	20 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	13.3 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	7.6 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	11.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	11.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	9 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	4.9 A
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	16 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1

SHORT-CIRCUIT PROTECTION RATING	20 A gG/gL, Fuse, Contacts
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.75 - 2.5) mm ² , ferrules to DIN 46228 2 x (0.75 - 2.5) mm ² , ferrules to DIN 46228
SUITABLE FOR	Branch circuits, suitable as motor disconnect, (UL/CSA) Front mounting
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-21, 240 V	1 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V	5 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	10 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V	10 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ	3 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400	4 kW

V, 50 HZ	
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	4 kW
RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 380/400 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 HZ	5.5 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RATED UNINTERRUPTED CURRENT (IU)	20 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	90 °
VOLTAGE PER CONTACT PAIR IN SERIES	60 V
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT)	10 kA, SCCR (UL/CSA) 20 A, Class J, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	5 kA, SCCR (UL/CSA) 50A, max. Fuse, SCCR (UL/CSA)
TERMINAL CAPACITY (SOLID/FLEXIBLE WITH FERRULE AWG)	18 - 14
TERMINAL CAPACITY (SOLID/STRANDED)	1 x (1 - 2.5) mm ² 2 x (1 - 2.5) mm ²
UNINTERRUPTED CURRENT	Rated uninterrupted current I _u is specified for max. cross-section.
DESIGN	15541

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

