

## Eaton 100547

Eaton Moeller® series E67 Proximity switch, optical, long range 100cm, 18-30VDC, NPN, PNP, dark, micro

<b>PRODUCT NAME</b>	Eaton Moeller® series E67 Proximity switch
<b>CATALOG NUMBER</b>	100547
<b>PRODUCT LENGTH/DEPTH</b>	160 mm
<b>PRODUCT HEIGHT</b>	57 mm
<b>PRODUCT WIDTH</b>	42 mm
<b>PRODUCT WEIGHT</b>	0.21 kg
<b>CERTIFICATIONS</b>	CE

<b>TYPE</b>	Optical sensors
<b>ELECTRIC CONNECTION TYPE</b>	Other
<b>FITTED WITH:</b>	Background suppression (Perfect Prox)
<b>ENCLOSURE MATERIAL</b>	Plastic
<b>ENCLOSURE TYPE</b>	Cuboid
<b>OPERATING MODE</b>	Switching principle: Dark switching
<b>EXPLOSION SAFETY CATEGORY FOR DUST</b>	None
<b>EXPLOSION SAFETY CATEGORY FOR GAS</b>	None
<b>FUNCTIONS</b>	Reflected-light beam
<b>VOLTAGE TYPE</b>	DC
<b>WIRE SIZE</b>	0
<b>CONNECTION TYPE</b>	4-wire Plug-in connection M12 x 1
<b>CABLE SHEATH MATERIAL</b>	Other
<b>LIGHT TYPE</b>	Infrared light
<b>DEGREE OF PROTECTION</b>	IP67 NEMA Other
<b>INTERFACE TYPE</b>	Other
<b>LED INDICATOR</b>	Status indication of Operating voltage: Green LED Status indication of Switching state: Red LED
<b>SWITCH FUNCTION TYPE</b>	Other
<b>LOAD CURRENT</b>	Max. 100 mA (I <sub>e</sub> )
<b>LASER PROTECTION CLASS</b>	None
<b>OPERATION AGENT-SAFETY CLASS</b>	Safety class 2
<b>SHOCK RESISTANCE</b>	30 g, Mechanical, Shock duration 6 ms
<b>OPTICAL SURFACE MATERIAL</b>	Plastic
<b>OUTPUT CURRENT (MA) - MAX</b>	100 mA
<b>OUTPUT CURRENT AT PROTECTED OUTPUT - MAX</b>	0 mA

<a href="#">IL05305005Z</a>	
<a href="#">eaton-proximity-switches-e67-proximity-switch-dimensions.eps</a>  <a href="#">eaton-proximity-switches-e67-proximity-switch-3d-drawing.eps</a>	

<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN</b>	0 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	30 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	18 V
<b>RATED SWITCHING DISTANCE (SN)</b>	1000 mm
<b>REFLECTOR DISTANCE - MIN</b>	0 mm
<b>SENSOR HEIGHT</b>	59 mm
<b>SENSOR LENGTH</b>	166 mm
<b>SWITCHING DISTANCE - MAX</b>	1300 mm
<b>SWITCHING VOLTAGE OF OSSD AT STATE HIGH</b>	30 V
<b>TRANSMISSION RANGE OF THE SAFETY FIELD</b>	0 m
<b>VOLTAGE RATING - MAX</b>	30 V
<b>SAFETY TYPE (IEC 61496-1)</b>	1
<b>SWITCHING FREQUENCY</b>	0 Hz
<b>SENSING MODE</b>	Dark switching
<b>SWITCHING OUTPUT TYPE</b>	PNP
<b>VIBRATION RESISTANCE</b>	10 Hz - 2 kHz, 10 g
<b>TRIANGULATION</b>	Background fade-out
<b>WAVELENGTH OF THE SENSOR</b>	0 nm
<b>WIDTH SENSOR</b>	43 mm
<b>PRODUCT CATEGORY</b>	E67 Long Range Series
<b>RESPONSE TIME</b>	15 ms
<b>ADJUSTMENT RANGE - MAX</b>	1000 mm

<b>ADJUSTMENT RANGE - MIN</b>	0 mm
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	55 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-35 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>DIAMETER SENSOR</b>	0 mm
<b>LIGHT DOT SIZE</b>	0 mm <sup>2</sup>
<b>NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION</b>	0
<b>NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)</b>	0
<b>NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)</b>	0
<b>NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)</b>	2
<b>OPERATING DISTANCE - MAX</b>	0 mm
<b>OPERATING DISTANCE - MIN</b>	0 mm
<b>OPERATING TEMPERATURE - MAX</b>	55 °C
<b>OPERATING TEMPERATURE - MIN</b>	-35 °C
<b>ADJUSTMENT TYPE</b>	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

