



□□□□

## Eaton 091694

Eaton Moeller series T5B Step switch, 63 A, Flush mounting, 6 contact unit(s), Contacts: 12, Maintained, 0-3, Design: 8481

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series T5B Step switch
<b>CATALOG NUMBER</b>	091694
<b>PRODUCT LENGTH/DEPTH</b>	174 mm
<b>PRODUCT HEIGHT</b>	88 mm
<b>PRODUCT WIDTH</b>	88 mm
<b>PRODUCT WEIGHT</b>	0.995 kg
<b>CERTIFICATIONS</b>	CE CSA-C22.2 No. 60947-4-1-14 CSA CSA Class No.: 3211-07 IEC/EN 60947 UL 60947-4-1 UL Category Control No.: NLRV CSA-C22.2 No. 94 VDE 0660 UL File No.: E36332 IEC/EN 60204 IEC/EN 60947-3 UL CSA File No.: 012528
<b>CATALOG NOTES</b>	Rated Short-time Withstand Current (I <sub>cw</sub> ) for a time of 1 second



Powering Business Worldwide

<b>TYPE</b>	Step switch
<b>ACTUATOR FUNCTION</b>	With 0 (Off) position Maintained
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	UV resistance only in connection with protective shield.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.

□□□□□	<a href="#">IL03801009Z</a>
□□□	<a href="#">eaton-rotary-switches-t0-step-switch-wiring-diagram-120.eps</a> <a href="#">eaton-rotary-switches-t0-step-switch-wiring-diagram-119.eps</a>
□□	<a href="#">eaton-rotary-switches-mounting-t5b-non-standard-switch-dimensions-006.eps</a> <a href="#">eaton-rotary-switches-front-plate-t0-step-switch-symbol-009.eps</a>

<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Black thumb grip and front plate 0 (off) position
<b>OPERATING FREQUENCY</b>	1200 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	63 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>SWITCHING ANGLE</b>	45 °
<b>VOLTAGE PER CONTACT PAIR IN SERIES</b>	24 V
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	0
<b>PRODUCT CATEGORY</b>	Control switches
<b>NUMBER OF POLES</b>	Four-pole
<b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>	22 kW
<b>DEVICE CONSTRUCTION</b>	Built-in device
<b>SWITCH TYPE</b>	Level switch

<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	1,3 kA, Contacts, 1 second
<b>ACTUATOR TYPE</b>	Toggle
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>	3 HP
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE</b>	7.5 HP
<b>ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE</b>	15 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>	10 HP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE</b>	15 HP
<b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>	40 HP
<b>ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE</b>	40 HP
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>MOUNTING POSITION</b>	As required
<b>MOUNTING METHOD</b>	Flush mounting
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	2 kA
<b>DEGREE OF PROTECTION</b>	NEMA 1 NEMA 12 IP65
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CONTROL CIRCUIT RELIABILITY</b>	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)

<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP65 NEMA 12
<b>NUMBER OF CONTACTS</b>	12
<b>SUITABLE FOR</b>	Branch circuits, suitable as motor disconnect, (UL/CSA) Front mounting
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	4.5 W
<b>NUMBER OF CONTACT UNITS</b>	6
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V</b>	3
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V</b>	1
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V</b>	6
<b>FRONT SHIELD SIZE</b>	88x88 mm
<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140
<b>SCREW SIZE</b>	M6, Terminal screw
<b>INSCRIPTION</b>	0-3
<b>SHOCK RESISTANCE</b>	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
<b>LIFESPAN, MECHANICAL</b>	500,000 Operations
<b>NUMBER OF SWITCH POSITIONS</b>	4
<b>LOAD RATING</b>	2 x I <sub>e</sub> (with intermittent operation class 12, 25 % duty factor) 1.3 x I <sub>e</sub> (with intermittent operation class 12, 60 % duty factor) 1.6 x I <sub>e</sub> (with intermittent operation class 12, 40 % duty factor)
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V</b>	2
<b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V</b>	3
<b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b>	520 A

<b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b>	600 A
<b>RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)</b>	480 A
<b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b>	340 A
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b>	800 A
<b>RATED OPERATING VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V</b>	33 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V</b>	23.8 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V</b>	51 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	41 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>	33 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V</b>	17 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS</b>	25 A
<b>SWITCHING CAPACITY (MAIN CONTACTS,</b>	63 A, Rated uninterrupted current max. (UL/CSA)

<b>GENERAL USE)</b>	
<b>SAFETY PARAMETER (EN ISO 13849-1)</b>	B10d values as per EN ISO 13849-1, table C.1
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V</b>	25 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V</b>	50 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V</b>	20 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V</b>	50 A
<b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V</b>	50 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 230 V</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 400 V</b>	63 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 500 V</b>	57.2 A
<b>RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 690 V</b>	29.4 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	63 A
<b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>	18.5 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>	30 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>	22 kW
<b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>	22 kW
<b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>	22 kW
<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	15 kW
<b>RATED OPERATIONAL</b>	18.5 kW

