



□□□□

## Eaton 092025

Eaton Moeller® series T5B Multi-speed switch, 63 A, rear mounting, 4 contact units, Contacts: 8, 60 °, maintained, 0 (Off) position, 1-0-2, Design number 8441

□□□□

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton Moeller® series T5B Multi-speed switch  |
| <b>CATALOG NUMBER</b>       | 092025  |
| <b>PRODUCT LENGTH/DEPTH</b> | 182 mm  |
| <b>PRODUCT HEIGHT</b>       | 88 mm   |
| <b>PRODUCT WIDTH</b>        | 88 mm   |
| <b>PRODUCT WEIGHT</b>       | 0.769 kg  |
| <b>CERTIFICATIONS</b>       | CSA-C22.2 No. 60947-4-1-14<br>IEC/EN 60204<br>UL File No.: E36332<br>UL<br>UL 60947-4-1<br>CE<br>UL Category Control No.: NLRV<br>VDE 0660<br>IEC/EN 60947<br>CSA-C22.2 No. 94<br>CSA Class No.: 3211-05<br>CSA<br>IEC/EN 60947-3<br>CSA File No.: 012528 |
| <b>CATALOG NOTES</b>        | Rated Short-time Withstand Current (Icw) for a time of 1 second   |



Powering Business Worldwide

□□□□

|   |  |
|---|--|
| <b>TYPE</b>   | Multi-speed switch   |
| <b>PRODUCT CATEGORY</b>   | Control switches   |
| <b>ACTUATOR FUNCTION</b>  | Maintained<br>With 0 (Off) position  |
| <b>10.10 TEMPERATURE RISE</b>   | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>  | Meets the product standard's requirements.   |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.   |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.   |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.   |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | UV resistance only in connection with protective shield.   |
| <b>10.2.5 LIFTING</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.6 MECHANICAL IMPACT</b>   | Does not apply, since the entire switchgear needs to be evaluated.   |
| <b>10.2.7 INSCRIPTIONS</b>  | Meets the product standard's requirements.   |
| <b>10.3 DEGREE OF PROTECTION OF</b>   | Does not apply, since the entire switchgear needs to   |

□□

|       |  |
|-------|--|
| □□□□□ | <a href="#">IL03801009Z</a>  |
| □□□   | <a href="#">eaton-rotary-switches-switch-t0-main-switch-wiring-diagram-010.eps</a>   |
| □□    | <a href="#">eaton-rotary-switches-mounting-t5b-non-standard-switch-dimensions-013.eps</a><br><a href="#">eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-009.eps</a> |

|   |  |
|---|--|
| <b>ASSEMBLIES</b>   | be evaluated.  |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                                     |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.             |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.   |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.   |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.   |
| <b>FITTED WITH:</b>   | 0 (off) position<br>Black thumb grip and front plate                           |
| <b>OPERATING FREQUENCY</b>                                      | 1200 Operations/h  |
| <b>POLLUTION DEGREE</b>   | 3  |
| <b>CLIMATIC PROOFING</b>  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| <b>ENCLOSURE MATERIAL</b>                                       | Plastic  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 6000 V AC  |
| <b>ACTUATOR TYPE</b>  | Short thumb-grip   |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 50 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>           | 40 °C  |
| <b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>           | -25 °C   |
| <b>ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE</b>        | 3 HP   |
| <b>ASSIGNED MOTOR POWER AT 200/208 V, 60</b>                    | 7.5 HP   |

|  |  |
|--|--|
| <b>HZ, 1-PHASE</b>   |  |
| <b>ASSIGNED MOTOR<br/>POWER AT 200/208 V, 60<br/>HZ, 3-PHASE</b>       | 15 HP  |
| <b>ASSIGNED MOTOR<br/>POWER AT 230/240 V, 60<br/>HZ, 1-PHASE</b>       | 10 HP  |
| <b>ASSIGNED MOTOR<br/>POWER AT 230/240 V, 60<br/>HZ, 3-PHASE</b>       | 15 HP  |
| <b>ASSIGNED MOTOR<br/>POWER AT 460/480 V, 60<br/>HZ, 3-PHASE</b>       | 40 HP  |
| <b>ASSIGNED MOTOR<br/>POWER AT 575/600 V, 60<br/>HZ, 3-PHASE</b>       | 40 HP  |
| <b>EQUIPMENT HEAT<br/>DISSIPATION, CURRENT-<br/>DEPENDENT PVID</b>     | 0 W  |
| <b>HEAT DISSIPATION<br/>CAPACITY PDISS</b>                             | 0 W  |
| <b>HEAT DISSIPATION PER<br/>POLE, CURRENT-<br/>DEPENDENT PVID</b>      | 4.5 W  |
| <b>NUMBER OF AUXILIARY<br/>CONTACTS (CHANGE-<br/>OVER CONTACTS)</b>    | 0  |
| <b>NUMBER OF AUXILIARY<br/>CONTACTS (NORMALLY<br/>CLOSED CONTACTS)</b> | 0  |
| <b>NUMBER OF AUXILIARY<br/>CONTACTS (NORMALLY<br/>OPEN CONTACTS)</b>   | 0  |
| <b>NUMBER OF CONTACT<br/>UNITS</b>                                     | 4  |
| <b>RATED SHORT-TIME<br/>WITHSTAND CURRENT<br/>(ICW)</b>                | 1,3 kA, Contacts, 1 second   |
| <b>ELECTRICAL<br/>CONNECTION TYPE OF<br/>MAIN CIRCUIT</b>              | Screw connection   |
| <b>MOUNTING POSITION</b>   | As required  |
| <b>RATED CONDITIONAL<br/>SHORT-CIRCUIT CURRENT<br/>(IQ)</b>            | 2 kA   |
| <b>MOUNTING METHOD</b>   | Rear mounting  |
| <b>OVERVOLTAGE<br/>CATEGORY</b>  | III  |
| <b>CONTROL CIRCUIT<br/>RELIABILITY</b>                                 | 1 failure per 100,000<br>switching operations<br>statistically determined, at<br>24 V DC, 10 mA) |

|  |   |
|--|---|
| <b>NUMBER OF POLES</b>                               | 3   |
| <b>DEGREE OF PROTECTION</b>                          | NEMA 12<br>IP65<br>NEMA 1   |
| <b>NUMBER OF CONTACTS</b>                            | 8   |
| <b>MODEL</b>   | Dahlander switch  |
| <b>DEGREE OF PROTECTION (FRONT SIDE)</b>             | IP65<br>NEMA 12   |
| <b>INSCRIPTION</b>                                   | 1-0-2   |
| <b>SWITCH FUNCTION TYPE</b>                          | One tapped winding, 2 speeds  |
| <b>LIFESPAN, MECHANICAL</b>                          | 500,000 Operations  |
| <b>SAFE ISOLATION</b>                                | 440 V AC, Between the contacts, According to EN 61140   |
| <b>RATED OPERATIONAL CURRENT (IE)</b>                | 63 A at AC-3, 230 V star-delta<br>57.2 A at AC-3, 500 V star-delta<br>63 A at AC-3, 400 V star-delta<br>29.4 A at AC-3, 690 V star-delta  |
| <b>SCREW SIZE</b>                                    | M6, Terminal screw  |
| <b>SHOCK RESISTANCE</b>                              | 15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms   |
| <b>LOAD RATING</b>                                   | 1.3 x I <sub>e</sub> (with intermittent operation class 12, 60 % duty factor)<br>2 x I <sub>e</sub> (with intermittent operation class 12, 25 % duty factor)<br>1.6 x I <sub>e</sub> (with intermittent operation class 12, 40 % duty factor) |
| <b>TIGHTENING TORQUE</b>                             | 4 Nm, Screw terminals<br>35.4 lb-in, Screw terminals  |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V</b> | 3   |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V</b>  | 1   |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V</b> | 6   |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V</b>  | 2   |
| <b>NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V</b>  | 3   |
| <b>RATED BREAKING</b>                                | 520 A   |

|  |   |
|--|---|
| <b>CAPACITY AT 220/230 V<br/>(COS PHI TO IEC 60947-3)</b>                        |   |
| <b>RATED BREAKING<br/>CAPACITY AT 400/415 V<br/>(COS PHI TO IEC 60947-3)</b>     | 600 A   |
| <b>RATED BREAKING<br/>CAPACITY AT 500 V (COS<br/>PHI TO IEC 60947-3)</b>         | 480 A   |
| <b>RATED BREAKING<br/>CAPACITY AT 660/690 V<br/>(COS PHI TO IEC 60947-3)</b>     | 340 A   |
| <b>RATED MAKING<br/>CAPACITY UP TO 690 V<br/>(COS PHI TO IEC/EN<br/>60947-3)</b> | 800 A   |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-21,<br/>440 V</b>                    | 63 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-23A,<br/>230 V</b>                   | 63 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-23A,<br/>400 V, 415 V</b>            | 63 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-23A,<br/>500 V</b>                   | 33 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-23A,<br/>690 V</b>                   | 23.8 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-3,<br/>220 V, 230 V, 240 V</b>       | 51 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-3,<br/>380 V, 400 V, 415 V</b>       | 41 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-3,<br/>500 V</b>                     | 33 A  |
| <b>RATED OPERATIONAL<br/>CURRENT (IE) AT AC-3,<br/>660 V, 690 V</b>              | 17 A  |
| <b>SWITCHING CAPACITY<br/>(MAIN CONTACTS,<br/>GENERAL USE)</b>                   | 63 A, Rated uninterrupted<br>current max. (UL/CSA)  |
| <b>SAFETY PARAMETER (EN<br/>ISO 13849-1)</b>                                     | B10d values as per EN ISO<br>13849-1, table C.1   |
| <b>SHORT-CIRCUIT<br/>PROTECTION RATING</b>                                       | 80 A gG/gL, Fuse, Contacts  |
| <b>TERMINAL CAPACITY<br/>(FLEXIBLE WITH<br/>FERRULE)</b>                         | 2 x (1.5 - 10) mm <sup>2</sup> , ferrule<br>to DIN 46228<br>1 x (1 - 25) mm <sup>2</sup> , ferrules<br>to DIN 46228 |

|   |   |
|---|---|
| <b>SUITABLE FOR</b>   | Branch circuits, suitable as motor disconnect, (UL/CSA)<br>Ground mounting<br>Intermediate mounting<br>Front mounting |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS</b> | 63 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS</b>  | 25 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V</b>                        | 25 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V</b>                         | 50 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V</b>                        | 20 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V</b>                         | 50 A  |
| <b>RATED OPERATIONAL CURRENT (IE) AT DC-23A, 60 V</b>                         | 50 A  |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>          | 63 A  |
| <b>RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ</b>                    | 18.5 kW   |
| <b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>                        | 30 kW   |
| <b>RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ</b>                        | 22 kW   |
| <b>RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ</b>                        | 22 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>                      | 37 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ</b>                          | 22 kW   |
| <b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>                          | 15 kW   |

