

Eaton 100NHFF00BI-400

Eaton Fuse-link, LV, 100 A, AC 400 V, NH00, gFF, IEC, dual indicator, insulated gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	100NHFF00BI-400
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	57 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	166 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	100 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH02
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	9 W
CONNECTION	Blade end
CONSTRUCTION	NH00
CONSTRUCTION SIZE	NH00
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch BVL50
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system A



**RATED SWITCHING
CAPACITY AC**

120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

