



## Eaton 101281

Eaton Moeller series xPole - PLI MCB.  
Miniature circuit breaker (MCB) with plug-in  
terminal, 4 A, 1p+N, characteristic: D

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - PLI MCB
<b>CATALOG NUMBER</b>	101281
<b>PRODUCT LENGTH/DEPTH</b>	84 mm
<b>PRODUCT HEIGHT</b>	75.5 mm
<b>PRODUCT WIDTH</b>	35 mm
<b>PRODUCT WEIGHT</b>	0.199 kg
<b>COMPLIANCES</b>	RoHS conform



*Powering Business Worldwide*

□□□□

<b>USED WITH</b>	Miniature circuit breaker PLI
<b>AMPERAGE RATING</b>	4 A
<b>FEATURES</b>	Concurrently switching N- neutral Additional equipment possible
<b>POLLUTION DEGREE</b>	2
<b>DEGREE OF PROTECTION</b>	IP20
<b>EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT</b>	1.6 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>TRIPPING CHARACTERISTIC</b>	D
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CURRENT LIMITING CLASS</b>	3
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT</b>	0 W

□□

□□□	<a href="#">eaton-xpole-mmc4-6-m- mcb-wiring-diagram.jpg</a>
□□□□	<a href="#">eaton-xpole-pli-mcb- catalog-ca019072en-en- us.pdf</a>
□□	<a href="#">eaton-xpole-pli-mcb- dimensions.jpg</a>

<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	2
<b>VOLTAGE TYPE</b>	AC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Single-pole + N
<b>RELEASE CHARACTERISTIC</b>	D
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• Miniature circuit breaker</li> <li>• PLI</li> </ul>
<b>SPECIAL FEATURES</b>	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole - Switchgear for residential and commercial applications</li> </ul>
<b>NUMBER OF POLES (PROTECTED)</b>	1
<b>NUMBER OF POLES (TOTAL)</b>	2
<b>RATED INSULATION VOLTAGE (UI)</b>	440 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	4 A
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	230 V
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V</b>	10 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V</b>	10 kA
<b>RATED SWITCHING CAPACITY (IEC/EN 60898-1)</b>	10 kA
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W
<b>POWER LOSS</b>	1.6 W

